


DETAIL "BU"  
 P/N A032  
 ALL DIMENSIONS SHOW IN THIS VIEW ARE BASIC

TOLERANCE UNLESS OTHERWISE NOTED  
 MILLIMETER  
 - PLACES ± - - -



DWG NO.	41ASH01126A
REV.	AR SHEET 68



8 | 7 | 6 | 5 | 4 | 3 | 2 | 1

H  
G  
F  
E  
D  
C  
B  
A

H  
G  
F  
E  
D  
C  
B  
A

SQ 19.95±0.05  
Ø0.5 A B C

SQ 21.1±0.05  
Ø0.5 A B C

2.2±0.08  
0.4±0.08  
0.6±0.08