










Title			Block
Size	Document Number	Rev	
A3	<Doc>	0	
Date:	Thursday, October 24, 2019	Sheet	2 of 10



Title		
Power		
Size	Document Number	Rev
A3	<Doc>	0
Date:	Thursday, October 24, 2019	Sheet 3 of 10







Title		
Size A3	Document Number <Doc>	Rev 0
Date: Thursday, October 24, 2019	Sheet 4	of 10







BOOT_MODE[1:0]	Boot Type
00	Boot From Fuses
01	Serial Downloader
10	Internal Boot
11	Reserved




FUSE	Settings
BOOT_CFG1[1:0]	Row address cycles 00-3 01-2 10-4 11-5
BOOT_CFG1[5:4]	Pages in block 00-128 01-64 10-32 11-256





Title		DRAM
Size	Document Number	Rev
A3	<Doc>	0
Date:	Thursday, October 24, 2019	Sheet 6 of 10





Title		
Ethernet		
Size A3	Document Number <Doc>	Rev 0
Date: Thursday, October 24, 2019	Sheet 8	of 10

