





Title		
Size	Number	Revision
A4		
Date:	2014/8/19	Sheet of
File:	E:\ _INTERFACE.SchDoc	Drawn By:




4.3寸TFT接口




背光




复位



触摸



ADS7843E/TS2046/XPT2046




SSD1963

TE:LCD刷新状态指示 36~39 51 GPIO PWM 用处??
TE:发送使能

Title		
Size	Number	Revision
A4		
Date:	2014/8/19	Sheet of
File:	E:\ \..LCD43.SchDoc	Drawn By:

OPENM4 - LCM4.3



Comment	Description	Designator	Footprint	LibRef	Quantity
100nF	Capacitor	C1, C5, C6, C7, C8, C9, C10, C11, C12, C13, C14, C15, C16, C17, C18, C20, C21, C22, C32, C33, C35, C36, C38, C39	0603A	CAP	24
10uF	Capacitor	C2	3216A	CAPACITOR	1
10uF	Capacitor	C3, C29	C0805	CAP, CAPACITOR	2
100nF	Capacitor	C4, C19, C34	C0805	CAP	3
5p	Capacitor	C23, C24	0603C	CAP	2
470nF	Capacitor	C25, C26, C27, C28	0603A	CAP	4
SS14	Default Diode	D1	DIO-DIODE	Diode	1
TP		FISH1	FISH	TP	1
TP		iDream1	LOGO500_T	TP	1
TFT4.3		J1	FPC-40-.5	TFT4.3	1
TP		JINGDIAN1	JINGDIAN	TP	1
22uH	IND,POWER,3A,R6 .7mm	L1	FB0805	INDUCTOR	1
22uH	IND,POWER,3A,R6 .7mm	L2	IND-SMD-A6_7	INDUCTOR	1
TP		MARK1, MARK2, MARK3, MARK4	MARK	TP	4
Header 20X2	Header, 20-Pin, Dual row	P1	2MMPIN40	Header 20X2	1
4.7K		R2, R3	0603R	RES1	2
1K	Resistor	R4	0603R	Res1	1
120R		R5	r0603	RES1	1
22R	Resistor	R6	0603R	Res1	1
15R	Resistor	R9	0603R	Res1	1
TP		TGND1, TGND2	HOLE125	TP	2
AMS1117-1.2V		U1	SOT-223	AMS1117-3.3V	1
SSD1963		U2	TQFP128/0.4	SSD1963	1
RT9293BGJ6		U3	SOT23-6	RT9293BGJ6	1
ADS7843E/TS2046/ XPT2046		U4	TSSOP16	TS2046	1
10M	Crystal	Y1	49S/SMD	CRYSTAL	1