



SCALE: 1/1



LCD type: TN Drive voltage: 3.2 V
 Display mode: Positive Duty: 1/4 Bias: 1/3
 Polarizer type: Reflective Operating Temp: -25 °C ~ 60 °C
 Viewing Angle: 6:00 Storage Temp: -25 °C ~ 75 °C
 Connector: PIN

PIN	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22
COM1	S3	S1	S5	S2	15D	rms	S35	10D	P4	11D	P5	12D	P6	13D	P7	14D	T1	1D	T2	S20	S27	2D
COM2	S7	S4	S9	S6	15E	15C	S18	10E	10C	11E	11C	12E	12C	13E	13C	14E	14C	1E	1C	S21	S24	2E
COM3	S15	S8	S11	S10	15F	15G	S17	10F	10G	11F	11G	12F	12G	13F	13G	14F	14G	1F	1G	S22	S25	2F
COM4	S16	S12	S13	S14	15A	15B	S19	10A	10B	11A	11B	12A	12B	13A	13B	14A	14B	1A	1B	S23	S26	2A

PIN	23	24	25	26	27	28	29	30	31	32	33	34	35	36	37	38	39	40	41	42	43	44
COM1	T3	3D	P1	4D	T4	5D	P2	6D	P3	L3	S37	7D	S34	8D	S33	9D	S32	S31	COM1			
COM2	2C	3E	3C	4E	4C	5E	5C	6E	6C	L2	S38	7E	7C	8E	8C	9E	9C	S29		COM2		
COM3	2G	3F	3G	4F	4G	5F	5G	6F	6G	L1	S39	7F	7G	8F	8G	9F	9G	S30			COM3	
COM4	2B	3A	3B	4A	4B	5A	5B	6A	6B	S36	S40	7A	7B	8A	8B	9A	9B	S28				COM4



SIRA		D E Ğ İ Ğ İ K L İ K		T A R İ H		AD I SOYADI		SIRA		D E Ğ İ Ğ İ K L İ K		T A R İ H		AD I SOYADI	
GEN. TOLERANS		AD I		ÜRÜN:		LK-LCD-REV2		AR-ELEKTRONİK		SAN. VE TIC. LTD. STİ.		BORNIVA CAD. NO: 14/16		İZMİR/TURKIYE	
JS 13		MALZEME:		TARİH:		AD I SOYADI		TEL: 0 232 436 05 17		FAX: 0 232 436 05 28		e mail: info@ar-elektronik.com		REV 2	
0-16 ±0.14		YÖZEY		KULLANIM		BRÜT		M. UÇAR		M. KARABAĞLI		RESİM NO:			
16-30 ±0.17		MİKTARI:		AD IRLIK:		ÇİZEN									
30-50 ±0.20		ÖLÇEK : 2/1		SAYFA NO:		KONTR									
50-80 ±0.25		KOD NO:				ONAY									
80-120 ±0.27															
120-180 ±0.32															
180-250 ±0.38															
250-315 ±0.41															
315-400 ±0.45															
400-500 ±0.49															
500-630 ±0.55															
630-800 ±0.62															
800-1000 ±0.71															