

- Board#1 U-Boot 2013.04 (Apr 22 2016 - 19:19:36)

```

=>md. | 0x0F010100
0f010100: ff001001 ff000e44 fe001001 ff000e44 ..... D..... D
0f010110: 00000641 fe002ec0 0d001001 fff00e34 ... A..... 4
0f010120: 80000801 fffc0e64 00000000 8b849612 ..... d.....
0f010130: 00000000 112183a0 00000000 a2141618 ..... !.....
0f010140: 00000000 110593da 00000000 87050410 .....
0f010150: 00000000 8501801a 00000000 8f25f1c7 ..... %..
0f010160: 8f25f1c7 8f25f1c7 2701340a 2701340a ..%..%.. 4. 4.
0f010170: 00000000 00000000 00000000 00000000 .....
0f010180: 00000000 1f000000 03d38210 03d38210 .....
0f010190: c249a466 00000000 c5000000 1e000000 . I. f.....
0f0101a0: 82000000 04000000 0f000a10 00000000 .....
0f0101b0: 00000000 00000000 00000000 82251590 ..... %..
0f0101c0: 81421490 04010101 111423fc 111423fc . B..... #. #.
0f0101d0: 111423fc 111423fc 111423fc 111423fc .. #. #. #. #.
0f0101e0: 111423fc 111423fc 111423fc 111423fc .. #. #. #. #.
0f0101f0: 111423fc 111423fc 111423fc 111423fc .. #. #. #. #.
=>

```

- Board#2 U-Boot 2013.04 (Apr 22 2016 - 19:19:36)

```

=>md. | 0x0F010100
0f010100: ff001001 ff000e44 fe001001 ff000e44 ..... D..... D
0f010110: 00000641 fe002ec0 0d001001 fff00e34 ... A..... 4
0f010120: 80000801 fffc0e64 00000000 ddafdb3a ..... d..... :
0f010130: 00000000 753a683c 00000000 c61565ff ..... u:h<..... e.
0f010140: 00000000 cb00e6fe 00000000 67e7fa7c ..... g. |
0f010150: 00000000 dc9e1b79 00000000 623b4bb9 ..... y.... b:K.
0f010160: 623b4bb9 623b4bb9 b9dba7e2 b9dba7e2 b;K. b;K.....
0f010170: 00000000 00000000 00000000 00000000 ..... \..... \
0f010180: 00000000 1f000000 60fcfdb9 60fcfdb9 .....
0f010190: c249a466 00000000 e9000000 1e000000 . I. f.....
0f0101a0: 94000000 e7000000 0f000a10 00000000 .....
0f0101b0: 00000000 00000000 00000000 52cff786 ..... R...
0f0101c0: bf46fed2 9ee9d88b 4c503d8b 4c503d8b . F..... LP=. LP=.
0f0101d0: 4c503d8b 4c503d8b 4c503d8b 4c503d8b LP=. LP=. LP=. LP=.
0f0101e0: 4c503d8b 4c503d8b 4c503d8b 4c503d8b LP=. LP=. LP=. LP=.
0f0101f0: 4c503d8b 4c503d8b 4c503d8b 4c503d8b LP=. LP=. LP=. LP=.
=>

```

- Board#3 U-Boot 2013.04 (Apr 22 2016 - 19:19:36)

```

=>md. | 0x0F010100
0f010100: ff001001 ff000e44 fe001001 ff000e44 ..... D..... D
0f010110: 00000641 fe002ec0 0d001001 fff00e34 ... A..... 4
0f010120: 80000801 fffc0e64 00000000 88868c50 ..... \d..... P
0f010130: 00000000 09116004 00000000 22032400 ..... ^..... $.
0f010140: 00000000 1892005e 00000000 53a2a043 ..... S. C
0f010150: 00000000 01376012 00000000 2206650d ..... 7..... e.
0f010160: 2206650d 2206650d 39319a20 39319a20 ". e." e. 91. 91.
0f010170: 00000000 00000000 00000000 00000000 .....
0f010180: 00000000 1f000000 610a040c 610a040c ..... a... a...
0f010190: c249a466 00000000 20000000 1e000000 . I. f.....
0f0101a0: 0e000000 02000000 0f000a10 00000000 .....
0f0101b0: 00000000 00000000 00000000 68419461 ..... hA. a
0f0101c0: 584800a0 aa808041 1902d841 1902d841 XH..... A... A... A
0f0101d0: 1902d841 1902d841 1902d841 1902d841 ... A... A... A... A
0f0101e0: 1902d841 1902d841 1902d841 1902d841 ... A... A... A... A
0f0101f0: 1902d841 1902d841 1902d841 1902d841 ... A... A... A... A
=>

```