

log: Trig @ 2019/10/08 13:33:53 (0:1:20.2 elapsed)

Type	Alias	Name	28	Value	29	0	32	64	96	128
*		SOM_IFC_A16		1						
*		SOM_IFC_A17		1						
*		SOM_IFC_A18		0						
*		SOM_IFC_AD[7]		1						
*		SOM_IFC_AD[6]		0						
*		SOM_IFC_AD[5]		0						
*		SOM_IFC_AD[4]		0						
*		SOM_IFC_AD[3]		0						
*		SOM_IFC_AD[2]		0						
*		SOM_IFC_AD[1]		0						
*		SOM_IFC_AD[0]		0						
*		SOM_IFC_CS <sub>n</sub>		0						
*		SOM_IFC_OE <sub>n</sub>		1						
*		SOM_IFC_WE <sub>n</sub>		0						

```

COM1 - PuTTY
In:  serial
Out: serial
Err: serial
TQM EEPROM:
  ID: TQMLS1021A-AD.0203
  SN: 71847137
  MAC: 00:d0:93:44:43:4b
SATA link 0 timeout.
AHCI 0001.0300 1 slots 1 ports ? Gbps 0x1 impl SATA mode
flags: 64bit ncq pm clo only pmp fbss pio slum part ccc
Found 0 device(s).
SCSI: Net:  Resetting Ethernet Phys...
Phy Resets Completed.
eTSEC1 is in sgmi mode.
eTSEC2 is in sgmi mode.
PCIe0: pcie@3400000 Root Complex: no link
PCIe1: pcie@3500000 disabled
eTSEC1, eTSEC2 [PRIME], eTSEC3
Hit any key to stop autoboot:  0
=> daadasd
Unknown command 'daadasd' - try 'help'
=> mw.b 0x6ff00000 0x1
=> mw.b 0x60000000 0x1
=>

```

log: Trig @ 2019/10/08 13:34:56 (0:1:3.0 elapsed)

Type	Alias	Name	28	Value	29	0	32	64	96	128
*		SOM_IFC_A16		1						
*		SOM_IFC_A17		1						
*		SOM_IFC_A18		0						
*		SOM_IFC_AD[7]		1						
*		SOM_IFC_AD[6]		0						
*		SOM_IFC_AD[5]		0						
*		SOM_IFC_AD[4]		0						
*		SOM_IFC_AD[3]		0						
*		SOM_IFC_AD[2]		0						
*		SOM_IFC_AD[1]		0						
*		SOM_IFC_AD[0]		0						
*		SOM_IFC_CS <sub>n</sub>		0						
*		SOM_IFC_OE <sub>n</sub>		1						
*		SOM_IFC_WE <sub>n</sub>		0						

```

COM1 - PuTTY
Out:  serial
Err:  serial
TQM EEPROM:
  ID: TQMLS1021A-AD.0203
  SN: 71847137
  MAC: 00:d0:93:44:43:4b
SATA link 0 timeout.
AHCI 0001.0300 1 slots 1 ports ? Gbps 0x1 impl SATA mode
flags: 64bit ncq pm clo only pmp fbss pio slum part ccc
Found 0 device(s).
SCSI: Net:  Resetting Ethernet Phys...
Phy Resets Completed.
eTSEC1 is in sgmi mode.
eTSEC2 is in sgmi mode.
PCIe0: pcie@3400000 Root Complex: no link
PCIe1: pcie@3500000 disabled
eTSEC1, eTSEC2 [PRIME], eTSEC3
Hit any key to stop autoboot:  0
=> daadasd
Unknown command 'daadasd' - try 'help'
=> mw.b 0x6ff00000 0x1
=> mw.b 0x60000000 0x1
=> mw.b 0x6ff00000 0x1
=>

```