

Modus: Unterschiede, Im Kontext

Linke Datei: D:\Projects\...\docs\NXP\Community_tickets\01_Debug_issues\Scenario_2_gdb_log.txt

Rechte Datei: D:\Projects\...\docs\NXP\Community_tickets\01_Debug_issues\Scenario_2_with_1st_fix_gdb_log.txt

10	cc = 0	=	10	cc = 0
11	config_string =		11	config_string =
12	ccs_get_cc_config; ccs_error = 23		12	ccs_get_cc_config; ccs_error = 23
13	Error message: CC not present		13	Error message: CC not present
14	ccs_config_cc		14	ccs_config_cc
15	serverh = 0		15	serverh = 0
16	config_string = s32dbg:169.254.190.174	<>	16	config_string = s32dbg:169.254.158.76
17	ccs_config_cc; ccs_error = 0	=	17	ccs_config_cc; ccs_error = 0
18	ccs_set_connection_timeout		18	ccs_set_connection_timeout
19	serverh = 0		19	serverh = 0
20	timeout = 100		20	timeout = 100
21	ccs_set_connection_timeout; ccs_error = 0		21	ccs_set_connection_timeout; ccs_error = 0
22	ccs config server		22	ccs config server
193	0x00000004 0x00000004 0x00000004 0x00000004	=	193	0x00000004 0x00000004 0x00000004 0x00000004
194	0x00000004 0x00000004 0x00000004 0x00000004		194	0x00000004 0x00000004 0x00000004 0x00000004
195	0x00000004 0x00000004 0x00000004 0x00000004		195	0x00000004 0x00000004 0x00000004 0x00000004
196	0x00000004 0x00000004 0x00000004 0x00000004		196	0x00000004 0x00000004 0x00000004 0x00000004
197	0x00000004 0x00000004 0x00000004 0x00000004		197	0x00000004 0x00000004 0x00000004 0x00000004
198	0x00000004 0x00000004 0x00000004 0x00000004		198	0x00000004 0x00000004 0x00000004 0x00000004
199	handle = 1	<>	199	handle = 3
200	ccs_add_register_group; ccs_error = 0	=	200	ccs_add_register_group; ccs_error = 0
201	ccs_read_register_group		201	ccs_read_register_group
202	serverh = 0		202	serverh = 0
203	cc = 0		203	cc = 0
204	handle = 1	<>	204	handle = 3
205	[chain_pos:1 index: 8192 count:1 size:4]	=	205	[chain_pos:1 index: 8192 count:1 size:4]
206	value: 00000000		206	value: 00000000
207	[chain_pos:1 index: 8193 count:1 size:4]		207	[chain_pos:1 index: 8193 count:1 size:4]
208	value: 00000000		208	value: 00000000
209	[chain_pos:1 index: 8194 count:1 size:4]		209	[chain_pos:1 index: 8194 count:1 size:4]
210	value: 00000001		210	value: 00000001
334	ccs_read_memory	=	334	ccs_read_memory
335	coreh = [serverh:0;cc_index:0;chain_pos:1]		335	coreh = [serverh:0;cc_index:0;chain_pos:1]
336	addr =		336	addr =
	[space:0;size:4;address_hi:0x00000000;address_lo:0x00000000]			[space:0;size:4;address_hi:0x00000000;address_lo:0x00000000]
337	data: (size = 4)		337	data: (size = 4)
338	D1010060		338	D1010060
339	ccs_read_memory; ccs_error = 0		339	ccs_read_memory; ccs_error = 0
340	ccs_read_memory	+-		
341	coreh = [serverh:0;cc_index:0;chain_pos:1]			
342	addr =			
	[space:0;size:4;address_hi:0x00000000;address_lo:0x40000200]			
343	data: (size = 4)			
344	D1010060			
345	ccs_read_memory; ccs_error = 76			
346	Error message: Bus error			
347	ccs_write_register	=	340	ccs_write_register
348	coreh = [serverh:0;cc_index:0;chain_pos:1]		341	coreh = [serverh:0;cc_index:0;chain_pos:1]
349	index = 8206		342	index = 8206
350	count = 1		343	count = 1
351	size = 4		344	size = 4
352	value: (size = 4)		345	value: (size = 4)
353	00000000		346	00000000
354	ccs_write_register; ccs_error = 0		347	ccs_write_register; ccs_error = 0
355	ccs_read_register_group		348	ccs_read_register_group
356	serverh = 0		349	serverh = 0
357	cc = 0		350	cc = 0
358	handle = 1	<>	351	handle = 3
359	[chain_pos:1 index: 8192 count:1 size:4]	=	352	[chain_pos:1 index: 8192 count:1 size:4]
360	value: 00000000		353	value: 00000000
361	[chain_pos:1 index: 8193 count:1 size:4]		354	[chain_pos:1 index: 8193 count:1 size:4]
362	value: 00000000		355	value: 00000000
363	[chain_pos:1 index: 8194 count:1 size:4]		356	[chain_pos:1 index: 8194 count:1 size:4]
364	value: 00000001		357	value: 00000001
488	ccs_read_memory	=	481	ccs_read_memory
489	coreh = [serverh:0;cc_index:0;chain_pos:1]		482	coreh = [serverh:0;cc_index:0;chain_pos:1]
490	addr =		483	addr =
	[space:0;size:4;address_hi:0x00000000;address_lo:0x00000000]			[space:0;size:4;address_hi:0x00000000;address_lo:0x00000000]
491	data: (size = 4)		484	data: (size = 4)
492	D1010060		485	D1010060
493	ccs_read_memory; ccs_error = 0		486	ccs_read_memory; ccs_error = 0
494	ccs_read_memory	+-		
495	coreh = [serverh:0;cc_index:0;chain_pos:1]			
496	addr =			
	[space:0;size:4;address_hi:0x00000000;address_lo:0x40000200]			
497	data: (size = 4)			
498	D1010060			
499	ccs_read_memory; ccs_error = 76			
500	Error message: Bus error			
501	ccs_multi_core_run_mode	=	487	ccs_multi_core_run_mode
502	chain_pos: (size = 1) { 1 (undefined) }		488	chain_pos: (size = 1) { 1 (undefined) }
503	ccs_multi_core_run_mode; ccs_error = 76		489	ccs_multi_core_run_mode; ccs_error = 76
504	Error message: Bus error		490	Error message: Bus error
505	ccs:Bus error		491	ccs:Bus error
506	ccs_run_multi_core		492	ccs_run_multi_core
507	chain_pos: (size = 0) { }		493	chain_pos: (size = 0) { }
508	ccs_run_multi_core; ccs_error = 6		494	ccs_run_multi_core; ccs_error = 6
509	Error message: Invalid parameter		495	Error message: Invalid parameter
510	ccs:Invalid parameter		496	ccs:Invalid parameter
		+-	497	ccs:Core disabled
511	ccs_run_core	=	498	ccs_run_core
512	coreh = [serverh:0;cc_index:0;chain_pos:1]		499	coreh = [serverh:0;cc_index:0;chain_pos:1]