



Measure	P1:period(C1)	P2:width(C1)	P3:width(C1)	P4:delay(C2)	P5:delay(C3)	P6:delay(C4)
value	---	9.73 ns	202.28 ns	-1.98 ns	8.23 ns	69.01 ns
status	⚠	✓	✓	✓	✓	✓

C1	C2	C3	C4
DCIM	DCIM	DCIM	DCIM
5.00 V/div	5.00 V/div	5.00 V/div	5.00 V/div
10.00 V offset	0.00 V offset	-10.00 V ofst	-18.30 V ofst
↓ 1.07 V	↓ 890 mV	↓ 310 mV	↓ 3.62 V
↑ -470 mV	↑ 2.72 V	↑ 3.13 V	↑ 3.02 V
Δy -1.54 V	Δy 1.83 V	Δy 2.81 V	Δy -600 mV

タイムベース	0 ns	トリガ	C1/DC
	50.0 ns/div	停止	750 mV
500 S	1.0 GS/s	エッジ	下向き
X1=	-1.0 ns	ΔX=	30.0 ns
X2=	29.0 ns	1/ΔX=	33.3 MHz