


DDR4 4GB x 32

Power supply voltage ramp:
 RESET_n is held LOW.
 VPP should be powered up before VDD/VDDQ



Note:
 16Gb x16 DualDie DDR4 SDRAM: Change R159 to 240ohm 1%, populate R158/R160, DNP R156
 16Gb x16 SingleDie DDR4 SDRAM: populate R156/R159 0-ohm, DNP R158/R160

Power supply voltage ramp:
 RESET_n is held LOW.
 VPP should be powered up before VDD/VDDQ

Note:
 16Gb x16 DualDie DDR4 SDRAM: Change R159 to 240ohm 1%, populate R158/R160, DNP R156
 16Gb x16 SingleDie DDR4 SDRAM: populate R156/R159 0-ohm, DNP R158/R160

Calixto
 INNOVATION
 BREAKTHROUGHS

Calixto Systems Pvt Ltd
 208, 2nd Floor, 4th Cross, 2nd Main,
 East of NCEEP Layout, Kestun Nagar,
 Bengaluru, Karnataka 560063.
 www.calixtosystems.com

Title		05 IMX8MM & DDR4	
Size	Document Number		<RevC>
C	<Doc>		
Date:	Tuesday, September 29, 2020	Sheet	5 of 14