kHz RANGE CRYSTAL UNIT SMD

MC-306 MC-405/MC-406

: 32.768 kHz (20 kHz to 165 kHz) •Frequency range Thickness : $8.0 \times 3.8 \times 2.54 \text{ mm} \cdot \cdot \cdot \text{MC-306}$ 10.41 × 4.06 × 3.6 mm ···MC-405/406

 Overtone order : Fundamental

 Applications : Clock and Microcomputer



Product Number (please contact us) MC-306 : Q1xMC3061xxxx00 MC-405 : Q1xMC4051xxxx00 : Q1xMC4061xxxx00 MC-406







Actual size

MC-306 MC-405/406 52.765k E 571

32.768k E 6571A


Specifications (characteristics)


Item	Symbol	Specifications		Conditions / Remarks	
Nominal frequency range	f_nom	32.768 kHz	20 kHz to 165 kHz	Please contact us regarding available frequencies	
Storage temperature	T_stg	-55 °C to +125 °C		Store as bare product.	
Operating temperature	T_use	-40 °C to +85 °C			
Level of drive	DL	1.0 μW Max.			
Frequency tolerance (standard)	f_tol	$\pm 20 \times 10^{-6}, \pm 50 \times 10^{-6}$	$\pm 50 \times 10^{-6}, \pm 100 \times 10^{-6}$	+25 °C, DL=0.1 μW	
Turnover temperature	Ti	+25 °C ±5 °C			
Parabolic coefficient	В	-0.04 × 10 ⁻⁶ / °C ² Max.			
Load capacitance	CL	6 pF to ∞ (standard :12.5 pF)		Please specify	
Motional resistance (ESR)	R1	50 kΩ Max.	As per below table		
Motional capacitance	C1	1.8 fF Typ.	4.0 fF to 0.6 fF	MC-306	
Initional capacitance		2.0 fF Typ.	4.0 IF 10 0.0 IF	MC-405 / 406	
Shunt capacitance	Co	0.9 pF Typ.	2.0 pF to 0.6 pF	MC-306	
		0.85 pF Typ.	2.0 pr to 0.6 pr	MC-405 / 406	
Frequency aging	f_age	$\pm 3 \times 10^{-6}$ / year Max.	$\pm 5 \times 10^{-6}$ / year Max.	+25 °C, First year	

Motional resistance (ESR)

Frequency	20 kHz≤f_nom< 31.2 kHz	31.2 kHz≤f_nom< 40 kHz	40 kHz≤f_nom< 90 kHz	90 kHz≤f_nom< 130 kHz	130 kHz≤f_nom≤165 kHz
Motional resistance	55 kΩ Max.	35 kΩ Max.	20 kΩ Max.	12 kΩ Max.	10 kΩ Max.


External dimensions





Footprint (Recommended)

(Unit:mm)



"QMEMS" EPSON TOYOCOM

In order to meet customer needs in a rapidly advancing digital, broadband and ubiquitous society, we are committed to offering products that are one step ahead of the market and a rank above the rest in quality. To achieve our goals, we follow a "3D (three device) strategy" designed to drive both horizontal and vertical growth. We will to grow our three device categories of "Timing Devices", "Sensing Devices" and "Optical Devices", and expand vertical growth through a combination of products from these categories.

A Quartz MEMS is any high added value quartz device that exploits the characteristics of quartz crystal material but that is produced using MEMS (micro-electro-mechanical system) processing technology.

Market needs are advancing faster than previously imagined toward smaller, more stable crystal products, but we will stay ahead of the curve by rolling out products that exceed market speed and quality requirements. We want to further accelerate the 3D strategy by QMEMS.

Quartz devices have become crucial in the network environment where products are increasingly intended for broadband, ubiquitous applications

and where various types of terminals can transfer information almost immediately via LAN and WAN on a global scale. Epson Toyocom Corporation addresses every single aspect within a network environment. The new corporation offers "Digital Convergence" solutions to problems arising with products for consumer use, such as, core network systems and automotive systems.



QMEMS and its logos are registered trademarks or trademarks of Seiko Epson Corporation in Japan and other countries.

PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Epson Toyocom, all environmental initiatives operate under the Plan-Do-Check-Action(PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites,in Japan and overseas, completed the acquisition of ISO 14001 certification.

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs.

Epson Toyocom made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired ISO/TS 16949 certification that is requested strongly by major automotive manufacturers as standard.

ISO/TS16949 is the international standard that added the sector-specific supplemental requirements for automotive industry based on ISO9001.

► Explanation of the mark that are using it for the catalog



►Pb free.



► Complies with EU RoHS directive.

*About the products without the Pb-free mark.

Contains Pb in products exempted by EU RoHS directive.

(Contains Pb in sealing glass, high melting temperature type solder or other.)



► The products have been designed for high reliability applications such as Automotive.

Notice

- This material is subject to change without notice.
- Any part of this material may not be reproduced or duplicated in any form or any means without the written permission of Epson Toyocom.
- The information, applied circuitry, programming, usage, etc., written in this material is intended for reference only. Epson Toyocom does not
 assume any liability for the occurrence of infringing on any patent or copyright of a third party. This material does not authorize the licensing for
 any patent or intellectual copyrights.
- Any product described in this material may contain technology or the subject relating to strategic products under the control of the Foreign
 Exchange and Foreign Trade Law of Japan and may require an export license from the Ministry of International Trade and Industry or other
 approval from another government agency.
- You are requested not to use the products (and any technical information furnished, if any) for the development and/or manufacture of weapon
 of mass destruction or for other military purposes. You are also requested that you would not make the products available to any third party
 who may use the products for such prohibited purposes.
- These products are intended for general use in electronic equipment. When using them in specific applications that require extremely high reliability, such as the applications stated below, you must obtain permission from Epson Toyocom in advance.
 - / Space equipment (artificial satellites, rockets, etc.) / Transportation vehicles and related (automobiles, aircraft, trains, vessels, etc.) / Medical instruments to sustain life / Submarine transmitters / Power stations and related / Fire work equipment and security equipment / traffic control equipment / and others requiring equivalent reliability.
- In this document, product codes and markings will remain as previously identified prior to the merger. Due to the on-going strategy of gradual unification of part numbers, please review product codes and markings.
- All brands or product names mentioned herein are trademarks and/or registered trademarks of their respective companies.