

FUSE MAP

	EVK Pull Down: 0 0/1	EVK Pull Down: 0 0/1	EVK Pull Down: 0 0/1	EVK Pull Down: 0 0/1	EVK Switch 0/1	EVK Pull Down: 0 0/1	EVK Pull Down: 0 0/1	EVK Pull Down: 0 0/1	EVK Pull Down: 0 0/1	EVK Switch 0/1
TYPE	BOOT_CFG[9]	BOOT_CFG[8]	BOOT_CFG[7]	BOOT_CFG[6]	BOOT_CFG[5]	BOOT_CFG[4]	BOOT_CFG[3]	BOOT_CFG[2]	BOOT_CFG[1]	BOOT_CFG[0]
FlexSPI1 - Serial NOR	HOLD TIME: 00 - 500us 01 - 1ms 10 - 3ms 11 - 10ms		0	0	0	0				FLASH_TYPE: 000-Device supports 3B read by default 001-Device supports 4B read by default 010-HyperFlash 1V8 011-HyperFlash 3V3 100-MXIC Octal DDR 101 - Micron Octal DDR 111 - QSPI device supports 3B read by default (on secondary pinmux option) (3B Read Means: QSPI 1 Byte command + 3 Byte Address.)
SD	SD/SDXC Speed: 00 - Normal/SDR12 01 - High/SDR25 10 - SDR50 11 - SDR104		0	0	1	Bus Width: 0 - 1-bit 1 - 4-bit	SD Power Cycle Enable: '0' - No power cycle '1' - Enabled via USDHC_RST pad	SD Loopback Clock Source Sel: (for SDR50 and SDR104 only) '0' - through SD pad '1' - direct	Part Select: 0 - eSDHC1 1 - eSDHC2	Fast Boot: 0 - Regular 1 - Fast Boot
FlexSPI1 - Serial NAND	"CS_INTERVAL: CS de-asserted interval between two commands 0 °C 100ns 1 °C 200ns 2 °C 400ns 3 °C 50ns"		1	1	BOOT_SEARCH _COUNT: 0 - 1 1 - 2	COL_ADDRESS _WIDTH: 0 °C 12bits 1 °C 13bits	SPI NAND HOLD TIME 00 - 0 us 01 - 500us 10 - 1ms 11 - 3ms	BOOT_SEARCH_STRIDE: Search Stride for FCB and DBBT (in terms of pages) 0 - 64 1 - 128 2 - 256 3 - 32		

