

i.MX50 EVK RD3 Linux

Release Notes

This document contains important information about the package contents, supported features, and known issues/limitations.

Contents

1	Release Contents	2
1.1	Contents	2
1.2	License	3
2	System Requirements.....	4
2.1	Linux Host Server	4
2.2	i.MX50 EVK RD3 Components	4
3	What's New.....	4
3.1	New Features	4
3.2	Defect Fixes.....	5
4	BSP Supported Features	5
5	Kernel Boot Parameters.....	7
6	Known Issues/Limitations.....	7



1 Release Contents

1.1 Contents

This release consists of the following four package files:

- L2.6.35_11.04.01_ER_images_MX5X.tar.gz
- L2.6.35_11.04.01_ER_source.tar.gz
- L2.6.35_11.04.01_ER_docs.tar.gz
- Mfgtools-Rel-11.04.01_ER.tar.gz

The release version is named as “L<Kernel_version>_<yy>.<mm>.<ij>”, where:

- <Kernel_version>: BSP Kernel version. “L2.6.35” indicates this BSP release is based on kernel version 2.6.35.
- <yy>.<mm>.<ij>”: Release time. For example, “10.12.00” indicates that this BSP is released on December, 2010.

[Table 1](#), [Table 2](#), [Table 3](#), and [Table 4](#) list the content included in the four package files.

Table 1 L2.6.35_11.04.01_ER_images_MX50.tar.gz Content

File	Description
u-boot-mx50-mDDR.bin	Uboot bootloader for the i.MX50 Armadillo2 board with mDDR
u-boot-mx50-lpDDR2.bin	Uboot bootloader for the i.MX50 Armadillo2 board with LPDDR2
u-boot-mx50-ddr2.bin	Uboot bootloader for the i.MX50 Armadillo2 board with DDR2
u-boot-mx50-rdp.bin	Uboot bootloader for the i.MX50 RDP board with LPDDR2
u-boot-mx50-rd3.bin	Uboot bootloader for the i.MX50 EVK RD3 board with LPDDR2
rootfs.ext2.gz	rootfs package
rootfs.jffs2	rootfs binary image
ulmage	Binary kernel image for the Linux 2.6.35 kernel. The same image can run in i.MX50/i.MX51/i.MX53 boards. It supports MX50 RDP/EVK RD3 board and ARM2 (mDDR/LPDDR2/DDR2) board.
zImage	Another format of above binary kernel image for the Linux 2.6.35 kernel.

Table 2 L2.6.35_11.04.01_ER_source.tar.gz Content

File	Description
EULA	Freescale End User License Agreement
install	Install script for LTIB
ltib.tar.gz	LTIB (Linux Target Image Builder)

File	Description
package_manifest.txt	Freescale LTIB open source packages
pkgs	Source and patches for the root file system
pkgs/ imx-test-11.04.01.tar.gz	Source code for the unit tests
pkgs/ imx-lib-11.04.01.tar.gz	Source code for the libraries
pkgs/ linux-2.6.35-imx_11.04.01.bz2	Freescale 2.6.35-11.04.01 kernel patches
pkgs/ u-boot-v2009.08-imx_11.04.01.tar.bz2	i.MX U-Boot patches based on U-Boot version 200908
pkgs/firmware-imx-11.04.01.tar.gz	i.MX firmware packages
pkgs/atheros-wifi-11.04.01.tar.gz	Source code of the Atheros WiFi AR6102 drivers
pkgs/ xserver-xorg-video-imx-11.04.01.tar.gz	Source code of the i.MX accelerated video driver
pkgs/tc-fsl-x86lnx-armeabi-nptl-4.1.2-3.i386.rpm	FSL Open source optimized toolchain gcc 4.1.2 for ARM9 and ARM11, which is used for i.MX profiles by default.
pkgs/gcc-4.4.4-glibc-2.11.1-multilib-1.0-1.i386.rpm	FSL Open source optimized toolchain gcc 4.4.4, which enables NEON for ARM cortex-A8.
pkgs/gcc-4.3.3-glibc-2.8-cs2009q1-203-1.i386.rpm	Codesourcery toolchain gcc 4.3.3.
tftp.zip	A Windows TFTP server program

Table 3 L2.6.35_11.04.01_ER_docs.tar.gz Content

File	Description
EULA	Freescale End User License Agreement
readme.html	Readme file containing links to additional documentation
doc/mx5	i.MX50 Linux BSP Release Notes, User's Guide.

Table 4 Mfgtools-Rel-11.04.01_ER.tar.gz Content

File	Description
Drivers	Host drivers
Profiles	Profiles for each platforms
Document	User manual for tool developers
Utils	cfimager.exe is used to flash boot images and create FAT partition on SD/MMC cards on the host PC. sb_loader.exe is used to download an image to target platform to run.
Manufacturing Tool Quick Start Manual.doc	Quick start manual for tool users
MfgTool.exe	Executable file

1.2 License

All Board Support Package (BSP) source-code files are GNU General Public License (GPL) or GNU Lesser General Public License (LGPL) or another open source license.

The following binary files, contained in the included root file systems, are built from proprietary source not included in the BSP:

- Files in package `libz160-bin_11.04.01.tar.gz`
- Files in package `amd-gpu-bin-mx51-11.04.01.tar.gz`

2 System Requirements

2.1 Linux Host Server

To build with LTIB or to program images to an MMC/SD card, it is necessary to set up an Ubuntu 9.04 Linux host server as described in [ltib_build_host_setup.pdf](#).

2.2 i.MX50 EVK RD3 Components

[Table 5](#) lists the hardware items contained in the i.MX50 EVK RD3 package.

Table 5 Kit Components

Item	Description
Boards	i.MX50 EVK RD3 Board (LPDDR2) Add-on board with E-Ink panel and keypad
Display	SEIKO WVGA panel
Cables	DB9 M/F RS-232 serial cable USB type A/M to MicroUSB type B/M, shielded cable Ethernet straight cable
Data storage	4 GB SD cards or above
Power Supply	100/240 VAC – 5 VDC, 3.8A, with AC adaptors
WiFi daughter card	Optional. WiFi SDIO daughter card for AR6102 or AR6003.

3 What's New

This section describes the changes in this release, including new features and defect fixes.

3.1 New Features

See [ResolvedEnhancements.html](#) for the complete list of new features and enhancements since the last release.

A summary of the main new features is as follows:

- **ENGR00141508:** Add new PMIC MC34708 driver support on EVK RD3
- **ENGR00140983:** Support SII902X HDMI on MX50 EVK RD3
- **ENGR00142123:** Add CLAA WVGA driver support on EVK RD3
- **ENGR00140486:** Add SPI NOR M25P32 Flash on EVK RD3
- **ENGR00142581:** Make SEIKO WVGA panel work on J12 on EVK RD3

3.2 Defect Fixes

See [ResolvedDefects.html](#), referenced inside the file `readme.html`, for the list of defects fixed in this release.

4 BSP Supported Features

[Table 6](#) describes the features that are supported in this BSP release.

Table 6 Supported Features

Feature	Supported?	Comments
Kernel		
Kernel	Yes	Kernel version: 2.6.35
File System	Yes	EXT2/EXT3/EXT4 are used as the file system in MMC/SD
Bootloader		
U-Boot	Yes	U-Boot delivery is based on U-Boot version 200908. Supports SPI NOR and MMC/SD slot1, slot2. Supports FEC and console output. Supports MMC4.4 (not tested on EVK RD3 board).
Machine Specific Layer		
ARM Core	Yes	Supports Cortex-A8 (800 MHz)
Memory	Yes	
Interrupt	Yes	
Clock	Yes	Control system frequency, clock tree distribution
Timer (GPT)	Yes	System timer tick support
GPIO/EDIO	Yes	GPIO is initialized in earlier phase according to hardware design. Note that all GPIO activate/deactivate functions used in the drivers are dummies (see the MSL code for details).
IOMUX	Yes	Provides the interfaces for I/O configuration
SPBA	No	
SDMA	Yes	
Character Device Drivers		
MXC UART	Yes	Console support through internal UART1/UART2/UART3
Graphic Drivers		
Frame Buffer Driver	Yes	MXC Frame buffer driver for both EDPC and ELCDIF
ePXP	Yes	Support RGB565→Y8 CSC, rotation, horizontal/vertical flip, etc.
DVI monitor	No	

Feature	Supported?	Comments
LVDS	No	
GPU	Yes	Supports GPU 2D. No 3D support in hardware.
Multimedia Drivers		
IPU V3 driver	No	
V4L2 Output/Capture	No	Support V4L2 output. No V4L2 capture support.
Camera	No	
TVOut	No	
TVIn	No	
VPU	No	
Power Management Drivers		
PMIC	Yes	Supports the MC34708 2.x PMIC through a SPI interface. Supports regulator management for voltage control.
Lower Power mode	Yes	Supports stop mode in mem state
DVFS-Core	Yes	Supported.
DVFS-Peripheral	No	
CPUFreq	Yes	
Bus scaling	Yes	
XEC	No	
Sound Drivers		
S/PDIF	No	
ASoC (SSI/AUDMUX)	Yes	Supports the STGL5000 stereo audio codec under ASoC framework Supports audio playback and record
ESAI/ CS42888	No	
Input Device Drivers		
Keypad	Yes	Supports keypad on Add-on board
Touch panel	Yes	Supports touch panel through MC34708 ADC on WVGA panel
USB devices	Yes	Supports USB mouse and USB keypad through USB ports
MTD driver		
SPI NOR	Yes	
NAND	Yes	Supports GPMI NAND, ONFI NAND, and Toggle NAND.
SATA	No	
Networking Drivers		
FEC	Yes	Supports LAN8720A PHY
MediaLB	No	
FlexCAN	No	
USB Drivers		
USB Host	Yes	Supports USB HOST1 and USB OTG host Note that USB OTG host mode is disabled by default in the MX5 configuration
USB Device	Yes	Supports USBOTG device mode
USBOTG	Yes	Support USB Host/device switch by ID PIN detection.
Security Drivers		
Security drivers	Yes	Supports DCP and RNGB
General drivers		
SRTC	Yes	
MC34708 RTC driver	Yes	The MC34708 RTC driver is enabled by default
MMC/SD/SDIO	Yes	Supports i.MX eSDHC module with PIO and DMA modes. (PIO mode not tested.) Supports eSDHC Slot 1 and Slot2 on the EVK RD3 board. Support eMMC4.4 DDR and SDR mode.
WatchDog	Yes	Supports Watchdog reset
I2C	Yes	Supports I2C master. Supports I2C1 and I2C2
SPI	Yes	Supports SPI master mode
PWM	Yes	Note pins for all PWM channels are used by other modules on the designed board

Feature	Supported?	Comments
USB BT dongle	Yes	Enables BLUEZ (not tested).
WiFi	Yes	Supports Atheros AR6102 and AR6003. AR6003 is enabled by default.

5 Kernel Boot Parameters

Depending on the booting/usage scenario, you may need different kernel boot parameters. [Table 7](#) lists some important kernel boot parameters.

Table 7 Kernel Boot Parameters

Kernel Parameters	Description	Typical Values	Used When
console	Where to output kernel logging by printk	console=ttyMXC0	All cases
ip	Tell kernel how/whether to get IP address	ip=none ip = dhcp ip=static_ip_address	"ip=dhcp" or "ip=static_ip_address" is mandatory in "boot from TFTP/NFS"
nfsroot	The location of the NFS server/directory	nfsroot=<ip_address>:<rootfs path>	Used in "boot from tftp/NFS" together with "root=/dev/nfs"
root	The location of the root file system	root=/dev/nfs or root=/dev/mmcblk0p2	Used in "boot from tftp/NFS" (for example, root=/dev/nfs) Used in "boot from SD" (for example, root=/dev/mmcblk0p2)
rootfstype	Indicates the file system type of the root file system	rootfstype=ext4	Used in "boot from SD" together with "root=/dev/mmcblk0p2"
rootwait	Wait (indefinitely) for root device to show up	rootwait	Used when mounting SD rootfs
hdmi	Enable Sii902x HDMI module	hdmi	Used when using HDMI
lcd	Indicates which LCD panel's used	lcd=1 lcd=1,j32 lcd=2	"lcd=1" when using SEIKO panel on J13 "lcd=1,j12" when using SEIKO panel on J12 "lcd=2" when using CLAA panel on J12

6 Known Issues/Limitations

You should read all hardware related materials and ensure the necessary hardware reworks are done before using the software. [Table 8](#) lists some key known issues.

Table 8 Known Issues and Workarounds

Features	Category	Description	Resolution/Workaround
FEC/ LCDIF Framebuffer	Hardware	SEIKO WVGA panel on J13 and FEC cannot be used simultaneously.	Designed board shares some pins.
MMC 4.4	Hardware	Not verified on EVK RD3 board because BGA-type card slot is not soldered.	Need board rework.
eMMC/SD	Hardware	Meet write CRC error when working with AHB at 24 MHz and SD CLK at 50 MHz	Not identified whether it is a hardware issue.
Keypad	Hardware	Keypad conflicts with Boot Configuration pins.	At the point when U-Boot is running but Keypad driver is not loaded yet, turn all Boot Configuration pins on SW5 to ON.
Keypad	Hardware	KEY_ROW0 is used as GPIO to set PWR_EN for SEIKO WVGA. If SEIKO WVGA panel works on J12, some keys are not functional.	Designed board shares the pin. No workaround.
Hardware Reset	Hardware/Software	When DVFS core is enabled, the hardware reset key can not reset the system.	Will be fixed in the upcoming release.

THIS PAGE INTENTIONALLY LEFT BLANK

How to Reach Us:**Home Page:**

www.freescale.com

Web Support:

<http://www.freescale.com/support>

USA/Europe or Locations Not Listed:

Freescale Semiconductor
Technical Information Center, EL516
2100 East Elliot Road
Tempe, Arizona 85284
+1-800-521-6274 or +1-480-768-2130
www.freescale.com/support

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH
Technical Information Center
Schatzbogen 7
81829 Muenchen, Germany
+44 1296 380 456 (English)
+46 8 52200080 (English)
+49 89 92103 559 (German)
+33 1 69 35 48 48 (French)
www.freescale.com/support

Japan:

Freescale Semiconductor Japan Ltd.
Headquarters
ARCO Tower 15F
1-8-1, Shimo-Meguro, Meguro-ku,
Tokyo 153-0064, Japan
0120 191014 or +81 3 5437 9125
support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor China Ltd.
Exchange Building 23F
No. 118 Jianguo Road
Chaoyang District
Beijing 100022
China
+86 010 5879 8000
support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution
Center
P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale and the Freescale logo are trademarks of Freescale Semiconductor, Inc. Reg. U.S. Pat. & Tm. Off. All other product or service names are the property of their respective owners. ARM is the registered trademark of ARM Limited. ARM Cortex A8 is a trademark of ARM Limited.

© Freescale Semiconductor, Inc. 2011. All rights reserved.

