



SUBJECT: Freescale i.MX6 Solo Lite

DATE: 21/11/2012



USB 2.0 High Speed Certification Report

Customer:
Freescale Semiconductors Inc.
6501, William Cannon Drive West
Austin, Texas
USA

Device:
i.MX6 Solo Lite

TID 40001449
USBD652

Supplier:
Testronic Labs Belgium nv.
Wetenschapspark 7
B-3590 Diepenbeek



TABLE OF CONTENT

1. Customer	3
2. Supplied Hardware and Software	3
2.1. Assets.....	3
2.2. General Embedded Host Information.....	3
2.3. Used measurement equipment by Testronic Labs.....	3
2.4. Test Tools.....	3
2.5. Test procedures	4
3. Summary of the performed tests	5
4. Results.....	6
4.1. Electrical Legacy	6
4.1.1. Upstream Full Speed Signal Quality	6
4.1.2. Device Inrush Current.....	9
4.1.3. Downstream Full Speed Signal Quality.....	10
4.1.4. Downstream Low Speed Signal Quality	13
4.1.5. Host Drop Test.....	15
4.2. Electrical High Speed	16
4.2.1. Upstream High Speed Signal Quality	16
4.2.2. Device Packet Parameters.....	18
4.2.3. Device CHIRP Timing.....	18
4.2.4. Device Suspend/Reset/Resume	18
4.2.5. Device Test J/K, SEO_NAK	19
4.2.6. Device Receiver Sensitivity	20
4.2.7. Downstream High Speed Signal Quality	21
4.2.8. Host Packet Parameters	24
4.2.9. Host CHIRP Timing.....	24
4.2.10. Host Suspend/Reset/Resume Timing	25
4.2.11. Host Test J/K, SEO_NAK	25
4.3. Device Framework	26
4.3.1. USB20CV Chapter 9	26
4.3.2. USBCV MSC.....	26
4.3.3. USB30CV	26
4.4. Power Measurements Device Mode	27
4.4.1. Windows 7 SP1 Power Measurement	27
4.4.1.1. Full Speed Mode	27
4.4.1.2. High Speed Mode.....	27
4.5. Back Voltage	27
4.6. Gold Tree (Interoperability)	28
4.6.1. Windows 7 SP1 Interoperability	28
4.7. A-UUT Interoperability.....	29
5. Other Testronic Labs services.....	30

1. CUSTOMER

Freescall Semiconductors Inc.
6501, William Cannon Drive West
Austin, Texas
USA

2. SUPPLIED HARDWARE AND SOFTWARE

2.1. ASSETS

Description	Manufacturer	Model
Product Under Test	Freescall	i.MX6 Solo Lite

Product under test has a High Speed Device and High speed Host port

2.2. GENERAL EMBEDDED HOST INFORMATION

Item	Info
Maximum rated current	500mA
Hub support	True 5 tier
How messages are displayed	Hyper Terminal
Support remote wakeup	False
TPL	MSC, Keyboard, Hub, Mouse

2.3. USED MEASUREMENT EQUIPMENT BY TESTRONIC LABS

Description	Manufacturer	Identity	Serial Nr
USB 2.0 Automated Software	Agilent	N5416A	
Differential Probe	Agilent	1169A	N10149
Pulse/Pattern generator	Agilent	81134A	MY42801040
Digital real-time oscilloscope	Agilent	DSA91304	MY50140172
Probe	Agilent	E2697A	MY43005817
Probe	Agilent	E2697A	MY50091034
Current probe	Tektronix	TCP202	B019512

2.4. TEST TOOLS

Description	Version
USB Electrical Analysis Tool "USBET20"	1.13
USB20CV	1.4.9.1
USB30CV	1.0.1.0



2.5. TEST PROCEDURES

Procedure		Version
Tools(USBET, USBCV)	http://www.usb.org/developers/tools/	
Updates	http://compliance.usb.org	
High Speed Device Electrical	http://www.usb.org/developers/compliance/	1.0
Low/Full Speed Test Procedure	http://www.usb.org/developers/USB-IFTestProc_1_3.pdf	1.3

3. SUMMARY OF THE PERFORMED TESTS

ELECTRICAL LEGACY

Upstream Full Speed Signal Quality	passed
Device Inrush	passed
Device Back Voltage	passed
Downstream Full Speed Signal Quality	passed
Downstream Low Speed Signal Quality	passed
Drop	passed

ELECTRICAL HIGH SPEED

Upstream High Speed Signal Quality	passed
Device Packet Parameters	passed
Device CHIRP Timing	passed
Device Suspend/Resume/Reset Timing	passed
Device Test J/K, SEO_NAK	passed
Device Receiver Sensitivity	passed
Downstream High Speed Signal Quality	passed
Host Packet Parameters	passed
Host CHIRP Timing	passed
Host Suspend/Resume/Reset Timing	passed
Host Test J/K, SEO_NAK	passed

DEVICE FRAMEWORK USBCV

USB20CV Chapter 9	passed
USB30CV Chapter 9	passed
USBCV MSC	passed

DEVICE POWER MEASUREMENTS

Power Measurements	passed
--------------------	--------

DEVICE GOLDEN TREE

Interoperability	passed
------------------	--------

EMBEDDED HOST INTEROPERABILITY


Functionality with TPL	passed
------------------------	--------

4. RESULTS


4.1. ELECTRICAL LEGACY

4.1.1. UPSTREAM FULL SPEED SIGNAL QUALITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the Full Speed Upstream Signal Quality test.



Signal Eye



Date and Common Mode Voltage


- eye passes
- EOP width: 166.20 ns
EOP width passes
- Measured signaling rate: 11.9993 MHz
signal rate passes
- Edge Monotonicity: 28 mV
Monotonic Edge passes
- Crossover voltage range: 1.51 V to 1.66 V, mean crossover 1.63 V
(first crossover at 1.51 V, 10 other differential crossovers checked)
crossover voltages pass
- Consecutive jitter range: -228.258 ps to 120.418 ps, RMS jitter 151.851 ps
- Paired JK jitter range: 16.196 ps to 18.917 ps, RMS jitter 17.610 ps
- Paired KJ jitter range: -53.849 ps to 22.646 ps, RMS jitter 31.246 ps
jitter passes

Additional Information

- Rising Edge Rate: 245.47 V/us (Equivalent risetime = 10.75 ns)
(minimum 132.00 V/us, maximum 660.00 V/us)
- Falling Edge Rate: 265.59 V/us (Equivalent falltime = 9.94 ns)
(minimum 132.00 V/us, maximum 660.00 V/us)
- Edge Rate Match: 7.87% (limit +/-10%)

4.1.1.2. DEVICE INRUSH CURRENT


The measured Inrush current of the Freescale Semiconductors Inc. i.MX6 Solo Lite is 8.68 μC . The USB spec allows up to 10 μF to be hard started, which represents an allowed load of approximately 50 μC . With a measured load of 8.68 μC , the device passed the inrush current test.




Inrush Current

4.1.3. DOWNSTREAM FULL SPEED SIGNAL QUALITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the Full Speed Downstream Signal Quality test.



Signal Eye



Date and Common Mode Voltage


- eye passes
- EOP width: 166.70 ns
EOP width passes
- Measured signaling rate: 11.9983 MHz
signal rate passes
- Edge Monotonicity: 4 mV
Monotonic Edge passes
- Crossover voltage range: 1.47 V to 1.68 V, mean crossover 1.63 V
(first crossover at 1.47 V, 19 other differential crossovers checked)
crossover voltages pass
- Consecutive jitter range: -267.110 ps to 236.798 ps, RMS jitter 132.651 ps
- Paired JK jitter range: -190.093 ps to 239.146 ps, RMS jitter 136.636 ps
- Paired KJ jitter range: -279.399 ps to 321.131 ps, RMS jitter 192.366 ps
jitter passes

Additional Information


- Rising Edge Rate: 274.41 V/us (Equivalent risetime = 9.62 ns)
(minimum 132.00 V/us, maximum 660.00 V/us)
- Falling Edge Rate: 158.12 V/us (Equivalent falltime = 16.70 ns)
(minimum 132.00 V/us, maximum 660.00 V/us)
- Edge Rate Match: 53.77% (limit +/-10%)

4.1.1.4. DOWNSTREAM LOW SPEED SIGNAL QUALITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the Low Speed Downstream Signal Quality test.



Signal Eye



- eye passes
- EOP width: 1.33 us
EOP width passes
- Measured signaling rate: 1.4998 MHz
signal rate passes
- Edge Monotonicity: 93 mV
Monotonic Edge passes
- Crossover voltage range: 1.34 V to 1.67 V, mean crossover 1.52 V
(first crossover at 1.65 V, 24 other differential crossovers checked)
crossover voltages pass
- Consecutive jitter range: -3.873 ns to 3.846 ns, RMS jitter 3.113 ns
- Paired JK jitter range: -0.489 ns to 1.230 ns, RMS jitter 0.572 ns
- Paired KJ jitter range: -0.698 ns to 0.906 ns, RMS jitter 0.508 ns
jitter passes

Additional Information

- Rising Edge Rate: 23.26 V/us (Equivalent risetime = 113.48 ns)
(minimum 8.80 V/us, maximum 35.20 V/us)
- Falling Edge Rate: 13.17 V/us (Equivalent falltime = 200.45 ns)
(minimum 8.80 V/us, maximum 35.20 V/us)
- Edge Rate Match: 55.40% (limit +/-20%)

4.1.5. HOST DROP TEST


The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the Drop test.

Load	Vbus (V)
No Load	5.19
500mA Load	5.05


4.2. ELECTRICAL HIGH SPEED

4.2.1. UPSTREAM HIGH SPEED SIGNAL QUALITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the High Speed Upstream Signal Quality test.



High Speed Signal Eye



Date and Common Mode Voltage

EL_2 USB 2.0 High-Speed transmitter data rate must be 480 Mb/s $\pm 0.05\%$

Data rate: 479.9677 MHz

Data rate: passed

EL_4 USB 2.0 upstream facing port on a device without a captive cable must meet Template 1 transform waveform requirements measured at TP3

passed

EL_6 USB 2.0 HS Driver must have 10 to 90% differential rise and fall times of greater than 500 ps.

passed

EL_7 USB 2.0 HS Driver must have monotonic data transitions over the vertical openings specified in the appropriate eye pattern template.

passed

4.2.2. DEVICE PACKET PARAMETERS

EL_21 The SYNC field for all transmitted packets (not repeated packets) must begin with a 32-bit SYNC field. Data Packets SYNC field: 64.62 ns
passed

EL_22 When transmitting after receiving a packet, hosts and devices must provide an inter-packet gap of at least 8 bit times and no more than 192 bit times.
Inter-packet gap: 331.68 ns
Inter-packet gap: 330.74 ns
passed

EL_25 The EOP for all transmitted packets (except SOFs) must be an 8-bit NRZ byte of 01111111 without bit stuffing.
NRZ byte: 17.06 ns
passed

4.2.3. DEVICE CHIRP TIMING

EL_28 Devices must transmit a chirp handshake no sooner than 2.5 μ s and no later than 6ms when being reset from suspend or full-speed state.
Chirp handshake: 1504 μ s
passed

EL_29 The chirp handshake generated by a device must be at least 1ms and not more than 7ms in duration.
Chirp handshake: 2.00 ms
passed

EL_31 During device speed detection, when a device detects a valid chirp K-J-K-J-K-J sequence, the device must disconnect its 1.5K pull-up resistor and enable its high speed terminations within 500 μ s. Disconnect time pull-up resistor: 3.71 μ s
passed

4.2.4. DEVICE SUSPEND/RESET/RESUME

EL_38 A device must revert to full-speed termination no later than 125 μ s after there is a 3ms idle period on the bus.
Full-speed revert time: 3.003 ms
passed

EL_39 A device must support the suspend state.
passed

EL_40 If a device is in the suspend state and was operating in high-speed before being suspended, then the device must transition back to high speed operation within two bit times from the end of resume time signaling

Note: It is not feasible to measure the device transition back to high-speed operation within two bit time from the end of the resume signaling. The presence of SOF at nominal 400mV amplitude following the resume signaling is sufficient for this test.

passed

EL_27 Devices must transmit a chirp handshake no sooner than 3.1ms and no later than 6ms when being reset from a non-suspended high-speed mode. The timing is measured from the beginning of the last SOF transmitted before the reset begins.

Chirp handshake: 3.50 ms

passed

EL_28 Devices must transmit a chirp handshake no sooner than 2.5 μ s and no later than 6ms when being reset from suspend or a full-speed state.

Chirp handshake: 1504 μ s

passed

4.2.5. DEVICE TEST J/K, SEO_NAK

EL_8 When either D+ or D- are driven high, the output voltage must be 400mV \pm 10% when terminated with precision 450 Ohm resistors to the ground

Test	D+ Voltage (mV)	D- Voltage (mV)
J	433	5
K	5	437

passed

EL_9 When either D+ or D- are not being driven, the output voltage must be 0V \pm 10mV when terminated with precision 450 Ohm resistors to the ground.

Test	Voltage (mV)
D+	0
D-	0

passed

4.2.6. DEVICE RECEIVER SENSITIVITY

EL_18 A high-speed capable device's Transmission Envelope Detector must be fast enough to allow the HS receiver to detect data transmission, active DLL lock, and detect the end of the SYNC field within 12 bit times.
passed

EL_17 A high-speed capable device must implement a transmission envelope detector that does not indicate squelch (i.e. reliably receives packets) when a receiver exceeds 150mV differential amplitude.
Note: A waiver may be granted if the receiver indicates Squelch at $\pm 50\text{mV}$ of 100mV differential amplitude. This is to compensate for the oscilloscope probe point away from the receiver pins.

Squelch:

155 mV

-121 mV

passed

EL_16 A high-speed capable device must implement a transmission envelope detector that indicates squelch (i.e. never receives packets) when a receiver's input falls below 100mV differential amplitude.

Note: A waiver may be granted if the receiver's input falls below 100mV differential amplitude. This is to compensate for the oscilloscope probe point away from the receiver pins.

Squelch:


154 mV

-118 mV


passed

4.2.7. DOWNSTREAM HIGH SPEED SIGNAL QUALITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the High Speed Downstream Signal Quality test.



High Speed Signal Eye



Date and Common Mode Voltage

Required Tests

- Overall result: pass!
- Signal eye:
eye passes
- EOP width: 7.95 bits
EOP width passes
- Measured signaling rate: 479.9693 MHz
signal rate passes
- Edge Monotonicity: 0 mV
Monotonic Edge passes
- Rising Edge Rate: 919.79 V/us (695.81 ps equivalent risetime)
passes
- Falling Edge Rate: 926.75 V/us (690.59 ps equivalent falltime)
passes

Additional Information

- Consecutive jitter range: -41.316 ps to 67.507 ps, RMS jitter 31.905 ps
- Paired JK jitter range: -63.710 ps to 64.639 ps, RMS jitter 18.393 ps
- Paired KJ jitter range: -67.641 ps to 59.986 ps, RMS jitter 14.476 ps

EL_2 USB 2.0 High-Speed transmitter data rate must be 480 Mb/s $\pm 0.05\%$
Data rate: 479.9600 MHz
passed

EL_3 USB 2.0 downstream facing port on a device without a captive cable must meet Template 1 transform waveform requirements measured at TP2
passed

EL_6 USB 2.0 HS Driver must have 10 to 90% differential rise and fall times of greater than 500 ps.
passed

EL_7 USB 2.0 HS Driver must have monotonic data transitions over the vertical openings specified in the appropriate eye pattern template.
passed

4.2.8. HOST PACKET PARAMETERS

EL_21 The SYNC field for all transmitted packets (not repeated packets) must begin with a 32-bit SYNC field. Since there is an internal hub it's allowed to truncate maximum 4 bits. SOF SYNC field and Data Packets SYNC both have 67.16 ns SYNC
passed

EL_25 The EOP for all transmitted packets (except SOFs) must be an 8-bit NRZ byte of 01111111 without bit stuffing. Since there is an internal hub it's allowed to add 4 random bits.
The EOP is 17 ns
passed

EL_23 Host transmitting two packets in a row must have an inter-packet gap of at least 88 bit times and not more than 192 bit times.
Inter-packet gap internally of the host is: 369 ns
Passed

EL_22 When transmitting after receiving a packet, hosts and devices must provide an inter-packet gap at least 8 bit times and not more than 192 bit times. Since there is an internal hub an additional delay is allowed with a maximum of 292 bit.
Inter-packet gap respond of a host packet is 360 ns
passed

EL_55 Host transmitting SOF packets must provide a 40-bit without bit stuffing where the first symbol of the EOP is a transition from the last data symbol. Since there is an internal hub it's allowed to add 4 random bits.
SOF EOP: 83.70 ns
passed

4.2.9. HOST CHIRP TIMING

EL_33 Downstream port start sending and alternating sequence of Chirp K's and Chirp J's within 100µs after the device Chirp K stops.
Measured value is 1.17 µs
passed

EL_34 Downstream port Chirp K and Chirp J durations must be between 40µs and 60µs duration.
Measured value is Chirp K 50.00 µs - Chirp J 50.00 µs
passed

EL_35 Downstream ports begin sending SOF's within 500µs and not sooner than 100µs from transmission of the last Chirp(J or K).
Measured value is: 360 µs
passed

4.2.10. HOST SUSPEND/RESET/RESUME TIMING

EL_39 A device must support the Suspend state.
passed

EL_41 After resuming a port, the host must begin sending SOF's within 3ms of the start of the idle state. When repeating the test of the SOF's never exceed the 3ms
The SOFs never exceed the 3ms when performing the test several times.
Passed

4.2.11. HOST TEST J/K, SEO_NAK

EL_8 When either D+ or D- are driven high, the output voltage must be 400mV +-10% when terminated with precision 45 Ohm resistors to the ground

	D+ Voltage (mV)	D- Voltage (mV)
J	427	5
K	5	431

passed

EL_9 When either D+ or D- are not being driven, the output voltage must be 0V +-10mV when terminated with precision 45 Ohm resistors to the ground.

	Voltage (mV)
D+	0
D-	0

passed

4.3. DEVICE FRAMEWORK

The following tests were performed using the USB20CV & USB30CV test tool.

4.3.1. USB20CV CHAPTER 9

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the Chapter 9 test of USB20CV.

Description	Full & High Speed
Vendor ID	15a2
Product ID	6c
CFG's	1
Interfaces	1
USB Spec.	2.0
Max. Power	2
Result	passed

4.3.2. USBCV MSC

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the USB20CV & USB30CV MSC test on Renesas and Fresco Logic xHCI.

4.3.3. USB30CV

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the USB30CV Chapter 9 test on Renesas and Fresco Logic xHCI.

4.4. POWER MEASUREMENTS DEVICE MODE

4.4.1. WINDOWS 7 SP1 POWER MEASUREMENT

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the power measurement tests.

4.4.1.1. FULL SPEED MODE

Device State	Measurement	Status
Unconfigured State	0.54 mA	passed
Configured State	0.54 mA	passed
Operating State	0.54 mA	passed
Suspended State	540.00 μ A	passed

4.4.1.2. HIGH SPEED MODE

Device State	Measurement	Status
Unconfigured State	0.54 mA	passed
Configured State	0.54 mA	passed
Operating State	0.54 mA	passed
Suspended State	540.00 μ A	passed

4.5. BACK VOLTAGE

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the back voltage tests.

	DC Voltage Before Enumeration	DC Voltage After Enumeration and Removal
Vbus	16 mV	16 mV
D+	0 mV	0 mV
D-	0 mV	0 mV

4.6. GOLD TREE (INTEROPERABILITY)

For more information about the test guides used by Testronic Labs Belgium n.v., please see the procedure that can be found at <http://compliance.usb.org>.

4.6.1. WINDOWS 7 SP1 INTEROPERABILITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the interoperability tests.

Test No.	Test description	Result
1	Enumeration and driver installation test on EHCI	passed
2	Remove External Power Supply	passed
3	DUT demonstrates correct using default drivers	passed
4	Update driver	n.a
5	Install Software	n.a
6	Demonstrates functionality with update driver and/or application	passed
7	Interoperability (operates all the devices in Gold Tree)	passed
8	Hot Detach & Reattach	passed
9	Warm boot	passed
10	Inactive S1 Suspend (Remote wake-up test)	passed
11	Inactive S1 Resume (Remote wake-up test)	passed
12	Active S3 Suspend	passed
13	Active S3 Resume	passed
14	UHCI Root port test	passed
15	Active S4 Suspend(Hibernate)	passed
16	Active S4 Resume(Hibernate)	passed
17	Topology change UHCI	passed
18	Topology change OHCI	passed
19	Topology change XHCI	passed

4.7. A-UUT INTEROPERABILITY

The Freescale Semiconductors Inc. i.MX6 Solo Lite passed the manual testing part (Chapter 7) of the USB On-The-Go and Embedded Host Automated Compliance Plan for the On-The-Go & Embedded Host Supplement Revision 2.0.

Test No.	Test Description	Result
7.3.1	Functionality B-device (specific TPL device(s))	passed
7.3.2	Category Functionality B-device Device 1	passed
	Device 2 (composite)	passed
7.3.3	Boot test	passed
7.3.4	Legacy Speed Test	passed
7.3.5	Concurrent and Independently test	passed
7.3.6	A-UUT Unsupported device message Test	passed
	Low Speed Device	passed
	Full Speed Device	passed
	High Speed Device	passed
	Super Speed Device	passed
	Composite Device	passed
7.3.7	A-UUT Hub Error Message test	passed
	Device behind Hub not enumerated	passed
7.3.8	A-UUT Hub functionality test	passed
	High Speed Device	passed
	Full Speed Device	passed
7.3.9	A-UUT Hub maximum tier test	passed
7.3.10	A-UUT Hub concurrent and independent test	passed
7.3.11	A-UUT Bus powered hub power exceeded test	passed
7.3.12	A-UUT Maximum concurrently device exceed message test	passed
7.3.13	A-UUT Suspend/Resume test	n.a.
7.3.14	A-UUT Suspend Disconnect test	n.a.
7.3.15	A-UUT Suspend Attach test	n.a.
7.3.16	A-UUT Suspend Topology Change test	n.a.
7.3.17	A-UUT Suspend Remote Wakeup test	n.a.
7.3.18	OTH to OTG Test	n.a.

5. OTHER TESTRONIC LABS SERVICES

Testronic Labs, Your hardware test centre.

Testronic Labs operates as an independent Belgian based test centre for the validation and release of multimedia peripheral equipment and interfaces.

Testronic Labs offers a wide range of testing activities and has become a professional test center for numerous companies all over the world, a test house known for its quality of testing and its dynamic approach.

Thanks to the independence of the test laboratories, Testronic Labs is ideally placed to offer an objective, third party opinion on overall quality of the products in development.

Currently, Testronic Labs experience is located in the following application areas:

Services:

- Alpha Testing
- Beta Testing
- Pre-WHQL Testing
- Compatibility Testing
- Functionality Testing
- Localisation Testing
- Spec Compliance
- Consultancy

Technologies:

- Optical Storage Drives
- Firewire IEEE1394 Certification
- PC, MAC systems and peripherals
- USB
- USB On-The-Go
- Serial-ATA
- Ethernet
- DLNA
- DVB
- PCI-Express
- HDMI, DVI
- Bluetooth
- WIFI
- ...

Tools:

- Ch8ck tool
- Traffic Lab

Please visit our web site at <http://www.testroniclabs.com> for detailed information regarding Testronic Labs testing services.