

Document Title	M101NWWB R3 Product Specification			Page No.	1/23
Document No.		Issue date	2016/03/15	Revision	0 0

Product Specification

To:

Product Name: M101NWWB R3

Document Issue Date: 2016/03/15

Customer	InfoVision Optoelectronics
SIGNATURE	SIGNATURE
	REVIEWED BY CQM
	PREPARED BY FAE
Please return 1 copy for your confirmation with your	
signature and comments.	

Note: 1. Please contact InfoVision Company. before designing your product based on this product.

2. The information contained herein is presented merely to indicate the characteristics and performance of our products. No responsibility is assumed by IVO for any intellectual property claims or other problems that may result from application based on the module described herein.

FQ-7-30-0-009-03D



Document Title	M101NWWB R3 Product Specification			Page No.	2/23
Document No.		Issue date	2016/03/15	Revision	0 0

Revision	Date	Page	Old Description	New Description	Remark
0 0	2016/03/15		_	First issue	
				X 4	



Document Title	M101NWWB R3 Product Specification			Page No.	3/23
Document No.		Issue date	2016/03/15	Revision	00

CONTENTS

1.0	GENERAL DESCRIPTIONS	4
2.0	ABSOLUTE MAXIMUM RATINGS	6
3.0	OPTICAL CHARACTERISTICS	7
4.0	ELECTRICAL CHARACTERISTICS	10
5.0	MECHANICAL CHARACTERISTICS	17
6.0	RELIABILITY CONDITIONS	19
7.0	PACKAGE SPECIFICATION	20
8.0	LOT MARK	21
9.0	GENERAL PRECAUTION	22

Document Title	M101NWWB R3 Product Specification			Page No.	4/23
Document No.		Issue date	2016/03/15	Revision	0 0

1.0 General Descriptions

1.1 Introduction

The M101NWWB R3 is a color active matrix thin film transistor (TFT) liquid crystal display (LCD) that uses amorphous silicon TFT as a switching device. This model is composed of aTFT LCD panel, a driver circuit and a backlight system. This TFT LCD has a 10.1 inch diagonally measured active display area with WXGA resolution (1280 horizontal by 800 vertical pixels array).

1.2 Features

- Supported WXGA Resolution
- LVDS Interface
- Wide View Angle
- Compatible with RoHS Standard

1.3 Product Summary


Items	·	Specifications	Unit
Screen Diagonal		10.1	inch
Active Area (H x V)		216.96 x135.60	mm
Number of Pixels (H)	(V)	1280x800	-
Pixel Pitch (H x V)		0.1695×0.1695	mm
Pixel Arrangement		R.G.B. Vertical Stripe	-
Display Mode		Normally Black	-
White Luminance		350 (Typ.)	cd /m ²
Contrast Ratio		800(Typ.)	-
Response Time		25(Typ.)	ms
Input Voltage		3.3 (Typ.)	V
Logical power consum	nption	1.2 (Max.)	W
(At White Pattern)		1.2 (Wdx.)	VV
Backlight power cons	umption	2.5 (Max.)	W
Weight		160(Max.)	g
Outline Dimension	w/o PCB	229.46(Typ.) ×149.1(Typ.)×2.8(Max.)	mm
(H x V x D)	w/ PCB	229.46(Typ.) ×149.1(Typ.)×4.56(Max.)	
Electrical Interface (Logic)		LVDS	-
Support Color		16.7 M	-
NTSC		45 (Typ.)	%
Viewing Direction		All	-
Surface Treatment		Glare , Hard –Coating 3H	-

InfoVision Optoelectronics (Kunshan)Co., Ltd.								
Document Title	M101NWWB R3 Product Specification			Page No.	5/23			
Document No.	Issue date 2016/0		2016/03/15	Revision	0 0			

1.4 Functional Block Diagram


Figure 1 shows the functional block diagram of the LCD module.

Figure 1 Block Diagram



1.5 Pixel Mapping

Figure 2 Pixel Mapping





Document Title	M101NWWB R3 Product Specification			Page No.	6/23
Document No.		Issue date	2016/03/15	Revision	0 0

2.0 Absolute Maximum Ratings

Table 1 Electrical & Environment Absolute Rating

Item	Symbol	Min.	Max.	Unit	Note
Logic Supply Voltage	V_{DD}	-0.3	4.0	V	(1),(2)
Operating Temperature	Тор	-20	70	$^{\circ}$	(2) (4) (5) (6)
Storage Temperature	Тѕт	-30	80	$^{\circ}$	(3),(4),(5),(6)
Vibration(Non-operating)	VB	-	1.5	G	(7)
Shock(Non-operating)	Shock	-	240	G	(8)

Note (1) Permanent damage may occur to the LCD module if beyond this specification. Functional operation should be restricted to the conditions described under normal operating conditions. Note (2) Operating temperature 25°C, humidity 55%RH.


Note (3) (T<=40 $^{\circ}$) Note static electricity.Maximum wet bulb temperature at 39 $^{\circ}$ C or less. (T>40 $^{\circ}$ C) No condensation.

Note (4) There is a possibility of causing deterioration in the irregularity and others of the screen and the display fineness though the liquid crystal module doesn't arrive at destruction when using it at $70\sim80^{\circ}$ C or $-30\sim-20^{\circ}$ C.

Note (5) There is a possibility of causing the fineness deterioration by the prolonged use in the (high temperature) humidity environment (60%RH or more).

Note (6) In the operating temperature item, the low temperature side is the ambient temperature regulations. The high temperature side is the panel surface temperature regulations.

Figure 3 Absolute Ratings of Environment of the LCD Module



Note (7) 10-500Hz, random vibration, 1h for X, Y, Z axis.

Note (8) 6ms, half sine wave, one time for X, Y, Z axis.

Document Title	M101NWWB R3 Product Specification			Page No.	7/23
Document No.		Issue date	2016/03/15	Revision	0 0

3.0 Optical Characteristics

The optical characteristics are measured under stable conditions as following notes.

Table 2 Optical Characteristics

Item	Conditions		Min.	Тур.	Max.	Unit	Note
	Horizontal	θ ×+	75	85	1		
Viewing Angle	Tiorizoritai	θ _{x-}	75	85	ı	dograo	(1) (2) (2)
(CR>10)	Vertical	θ _{y+}	75	85	ı	degree	(1),(2),(3)
	vertical	θ _{y-}	75	85	ı	*	
Contrast Ratio	Center		600	800			(1),(2),(4)
Contrast Natio	Center		000	800	-	-	θx=θy=0°
Response Time	Rising + Falling	a	_	25	50	ms	(1),(2),(5)
response rime	Trising + Family	9	_	25	30	Шэ	θx=θy=0°
	Red x			0.582		-	
	Red y			0.347		-	
Color	Green x		Typ.	0.349	Тур.	-	
	Green y		-0.03	0.573	+0.03	-	(1),(2),(3)
Chromaticity	Blue x			0.164		-	θx=θy=0°
(CIE1931)	Blue y			0.143		-	
	White x		Тур.	0.313	Тур.	-	
	White y		-0.03	0.329	+0.03	-	
NTSC			42	45		%	(1),(2),(3)
NISC	_		42	40		70	θx=θy=0°
White Luminance	Center		300	350	1	cd/m^2	(1),(2),(6)
Luminance	9 Points		70	75		%	(1),(2),(6)
Uniformity	3 FUIIILS		70	70	-	/0	θx=θy=0°


Note (1) Measurement Setup:

The LCD module should be stabilized at given temperature(25°C) for 15 minutes to avoid abrupt temperature change during measuring. In order to stabilize the luminance, the measurement should be executed after lighting backlight for 15 minutes in a windless room.



Document Title	M101NWWB R3 Product Specification				8/23
Document No.		Issue date	2016/03/15	Revision	0 0

Figure 4 Measurement Setup




Note (2) The LED input parameter setting as:

I_LED: 80mA

PWM_LED: duty 100 %

Note (3) Definition of Viewing Angle

Figure 5 Definition of Viewing Angle



Note (4) Definition Of Contrast Ratio (CR)

The contrast ratio can be calculated by the following expression

Contrast Ratio (CR) = L255 / L0


L255: Luminance of gray level 255, L0: Luminance of gray level 0

Note (5) Definition Of Response Time (T_R, T_F)



Document Title	M101NWWB R3 Produc	M101NWWB R3 Product Specification				
Document No.		Issue date	2016/03/15	Revision	0 0	


Figure 6 Definition of Response Time



Note (6) Definition Of brightness Luminance Measure the luminance of gray level 255 at 9 points. Luminance Uniformity= Min.(L1, L2, ... L9) / Max.(L1, L2, ... L9)

H—Active Area Width, V—Active Area Height, L—Luminance

Figure 6 Measurement Locations of 9 Points



Document Title	M101NWWB R3 Produc	M101NWWB R3 Product Specification				
Document No.		Issue date	2016/03/15	Revision	00	

4.0 Electrical Characteristics

4.1 Interface Connector

Table 3 Signal Connector Type

Item	Description	
Manufacturer / Type	Starconn / 300E40-0010RA-G3	
Mating Receptacle / Type (Reference)	111B40-1211TA-G3 or Compatible	

Table 4 Signal Connector Pin Assignment

Pin#	Signal Name	Description	Remarks
1	NC	No Connection	-
2	VDD	Power Supply	-
3	VDD	Power Supply	<u>-</u>
4	VDD_EDID	VDD_EDID	-
5	SCL_EDID	SCL_EDID	-
6	SDA_EDID	SDA_EDID	-
7	NC	No Connection	-
8	LV0N	-LVDS Differential Data Input	
9	LV0P	+LVDS Differential Data Input	-
10	GND	Ground	-
11	LV1N	-LVDS Differential Data Input	-
12	LV1P	+LVDS Differential Data Input	
13	GND	Ground	-
14	LV2N	-LVDS Differential Data Input	
15	LV2P	+LVDS Differential Data Input	-
16	GND	Ground	-
17	LVCLKN	-LVDS Differential Clock Input	-
18	LVCLKP	+LVDS Differential Clock Input	
19	GND	Ground	-
20	LV3N	-LVDS Differential Data Input	_
21	LV3P	+LVDS Differential Data Input	_
22	GND	Ground	-
23	LED_GND	Ground for LED Driving	-
24	LED_GND	Ground for LED Driving	-
25	LED_GND	Ground for LED Driving	-
26	NC	No Connection	-



Document Title	M101NWWB R3 Produc	Page No.	11/23		
Document No.		Issue date	2016/03/15	Revision	0 0

27	LED_PWM	PWM Input Signal for LED Driver	-
28	LED_EN	LED Enable Pin	-
29	NC	Reserved For CABC	-
30	NC	No Connection	
31	LED_VCC	Power Supply for LED Driver	
32	LED_VCC	Power Supply for LED Driver	
33	LED_VCC	Power Supply for LED Driver	
34	NC	No Connection	
35	BIST	BIST pin	Active high
36	NC	No Connection	4 A U
37	NC	No Connection	
38	NC	No Connection	
39	NC	No Connection	
40	NC	No Connection	

4.2 Signal Electrical Characteristics

4.2.1 Signal Electrical Characteristics For LVDS Receiver

The built-in LVDS receiver is compatible with (ANSI/TIA/TIA-644) standard.

Table 5 LVDS Receiver Electrical Characteristics

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Differential Input High Threshold	Vth	_	ı	+100	mV	V _{CM} =+1.2V
Differential Input Low Threshold	Vtl	-100	ı	1	mV	V _{CM} =+1.2V
Magnitude Differential Input Voltage	$ V_{ID} $	100	-	600	mV	-
Common Mode Voltage	V _{CM}	VID /2	1	2.4- V _{ID} /2	٧	-

Note (1) Input signals shall be low or Hi- resistance state when VDD is off.

Note (2) All electrical characteristics for LVDS signal are defined and shall be measured at the interface connector of LCD.

	nfoVision Optoelectronic	cs (Kuns	han)Co.,	Ltd.	
Document Title	M101NWWB R3 Product Specification				12/23
Document No.		Issue date	2016/03/15	Revision	0 0

Figure 8 Voltage Definitions





Figure 9 LVDS Data Mapping





Document Title	M101NWWB R3 Produc	Page No.	13/23		
Document No.		Issue date	2016/03/15	Revision	0 0


4.3 Interface Timings

Table 6 Interface Timings

Parameter	Symbol	Unit	Min.	Тур.	Max.
Frame Rate		Hz	-	60	-
Frame Period	Tv	line	815	823	1023
Vertical Display Time	TVD	line		800	
Vertical Blanking Time	Tvw+Tvbp+Tvfp	line	15	23	33
1 Line Scanning Time	Тн	clock	1410	1440	1470
Horizontal Display Time	THD	clock		1280	
Horizontal Blanking Time	THW+THBP+THFP	clock	60	160	190
Clock Rate	1/Tc	MHz	68.9	71.1	73.4

4.3.1 Timing Diagram of Interface Signal (DE mode)

Figure 10 Timing Characteristics



IVO In	nfoVision Optoelectronic	cs (Kuns	han)Co.,	Ltd.	
Document Title	M101NWWB R3 Product Specification			Page No.	14/23
Document No.		Issue date	2016/03/15	Revision	0 0

4.4 Input Power Specifications

Input power specifications are as follows.

Table 7 Input Power Specifications


Parameter		Symbol	Min.	Тур.	Max.	Unit	Note
System Power	r Supply						
LCD Drive Vol	tage (Logic)	V_{DD}	3.0	3.3	3.6	V	(2), (4)
VDD Current White Pattern		l _{DD}	-	0.295	ı	A	(3),(4),
VDD Power Consumption	White Pattern	P _{DD}	-	-	1.2	w	(3),(4),
Rush Current		I _{Rush}	-	-	1.5	А	(1),(4),(5)
Allowable Logi	c/LCD	W			300	mV	(4)
Drive Ripple V	oltage	V_{VDD-RP}	ı		300	IIIV	(4)
LED Power S	иррІу						
LED Input Volt	age	V_{LED}	6	12	21	V	(4)
LED Power Co	LED Power Consumption			-	2.5	W	(4)
LED Forward \	LED Forward Voltage LED Forward Current		2.8	-	3.2	V	
LED Forward			-	20	ı	mA	
PWM Signal	High	1	3.0	-	3.6	V	(4)
Voltage	Low	V_{PWM}	0	-	0.4	V	(4)
LED Enable	High	V	3.0	-	3.6	V	
Voltage	Low	$V_{LED_{EN}}$	0	-	0.4	V	
			100	ı	200		D _{DIM} ≥0.1%
			200	ı	500		D _{DIM} ≥0.25%
			500	ı	1000		D _{DIM} ≥0.5%
Input DWM Er	auanay	F_PWM	1000	-	2000	Hz	D _{DIM} ≥1%
input Pyvivi Fit	Input PWM Frequency		2000	-	5000	112	D _{DIM} ≥2.5%
			5000	-	10000		D _{DIM} ≥5%
			10000	-	20000		D _{DIM} ≥10%
			20000	-	30000		D _{DIM} ≥15%
LED Life Time		LT	20,000	25,000	-	Hours	(3)(6)



Document Title	M101NWWB R3 Product Specification			Page No.	15/23
Document No.		Issue date	2016/03/15	Revision	0 0

Note (1) Measure Condition


Figure 9 VDD Rising Time




Note (2) VDD Power Dip Condition

V_{TH}< V_{DD}≤ Vmin, td≤ 10ms (a time of the voltage return to normal), our panel can revive automatically.

Figure 10 VDD Power Dip



- Note (3) Frame Rate=60Hz, VDD=3.3V, DC Current.
- Note (4) Operating temperature 25°C, humidity 55%RH.
- Note (5) The reference measurement circuit of rush current.





Ī	Document Title	M101NWWB R3 Product Specification			Page No.	16/23
	Document No.		Issue date	2016/03/15	Revision	0 0

Note (6) The LED life time define as the estimated time to 50% degradation of initial luminous.

4.5 Power ON/OFF Sequence

Interface signals are also shown in the chart. Signals from any system shall be Hi- resistance state or low level when VDD voltage is off.




Figure 11 Power Sequence

Table 8 Power Sequencing Requirements

Parameter	Symbol	Unit	Min	Тур.	Max
VIN Rise Time	T1	ms	0.5		10
VIN Good to Signal Valid	T2	ms	30		90
Signal Valid to Backlight On	Т3	ms	200	-	
Backlight Power On Time	T4	ms	0.5		
Backlight VDD Good to System PWM On	T5	ms	10	-	
System PWM ON to Backlight Enable ON	Т6	ms	10	-	
Backlight Enable Off to System PWM Off	T7	ms	0		
System PWM Off to B/L Power Disable	Т8	ms	200		
Backlight Power Off Time	Т9	ms	0.5	10	30
Backlight Off to Signal Disable	T10	ms	200		
Signal Disable to Power Down	T11	ms	0		50
VIN Fall Time	T12	ms	0.5	10	30
Power Off	T13	ms	500		




Document Title	M101NWWB R3 Product Specification				17/23
Document No.		Issue date	2016/03/15	Revision	0 0

5.0 **Mechanical Characteristics**

5.1 Outline Drawing


Figure 12 Outline Drawing (Front Side)





	nfoVision Optoelectronic	cs (Kuns	han)Co.,	Ltd.	
Document Title	M101NWWB R3 Product Specification			Page No.	18/23
Document No.		Issue date	2016/03/15	Revision	0 0

Figure 13 Outline Drawing (Back Side)



5.2 Dimension Specifications

Table 9 Module Dimension Specifications

Parameter	Min	Тур	Max	Unit				
Width	229.06	229.46	229.86	mm				
Height	148.7	149.1	149.5	mm				
Depth w/o PCB	2.2	2.5	2.8	mm				
Depth w/ PCB	-	-	4.56	mm				
Weight	-	-	160	g				



Document Title	M101NWWB R3 Product Specification			Page No.	19/23
Document No.		Issue date	2016/03/15	Revision	0 0

6.0 Reliability Conditions

Item	Package	Test Conditions	Note
High Temperature Operating Test	Module	70℃, 240 hours	(1),(2),(3),(4)
Low Temperature Operating Test	Module	-20°C, 240 hours	(1),(2),(3),(4)
High Temperature Storage Test	Module	80°C, 240 hours	(1),(2),(4)
Low Temperature Storage Test	Module	-30°C, 240 hours	(1),(2),(4)
High Temperature/High Humidity Operating Test	Module	60°C, 90%RH, 240 hours	(1),(2),(3),(4)
Shock Non-operating Test	Module	240G, 2ms, 1time for ±x, ±y, ±z 6 directions	(4)
Vibration Non-operating Test	Module	1.5G , 10~500 Hz , x、y、z each axis/1hour.	(4)
ESD Test	Module	150pF/330ohm, air ±15KV, contact ±8KV	(5)

Note (1) All the judgments are under room temperature and the sample need to be static more than 2 hours in the room temperature before judge.

Note (2) During measurement, the condensation water or remains shall not be allowed.

Note (3) In operating test, the backlight voltage and current must be in speccfication.

Note (4) There is no display function issue occurred, all the cosmetic specification is judged before the reliability stress.


Note (5) In case of malfunction defect caused by ESD damage. If it would be recovered to normal state after resetting, it would be judge as pass.



IVO I	nfoVision Optoelectronic	cs (Kuns	han)Co.,	Ltd.	
Document Title	M101NWWB R3 Product Specification			Page No.	20/23
Document No.		Issue date	2016/03/15	Revision	0 0

7.0 Package Specification


Figure 14 Packing Method





Document Title	M101NWWB R3 Product Specification				21/23
Document No.		Issue date	2016/03/15	Revision	0 0

8.0 Lot Mark



Note: This picture is only an example.

8.1 20 Lot Mark

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
									40000	- 4	, I	DE-							

Code 1,2,4,5,6,7,8,9,10,11,16: IVO internal flow control code.

Code 3: Production Location.

Code 12: Production Year.

Code 13: Production Month.

Code 14,15: Production Day.

Code 17,18,19,20: Serial Number.

8.2 23 Product Barcode

Code 1,2: Manufacture District.

Code 3,4,5,6,7: IVO internal module name.

Code 8,9,10,13,16: IVO internal flow control code.

Code 11,12: Cell location Suzhou, China defined as "KS".

Code 14 ,15: Module location Kunshan, China defined as "KS"; Yangzhou, China defined as "YZ"; Shenzhen, China defined as "SE"; Zhuhai, China defined as "ZH"; Suzhou, China defined as "SZ".

Code 17,18,19: Year, Month, Day refer to Note(1), Note(2) and Note(3).

Note (1) Production Year

Year	2006	2007	2008	2009	2010	2011	2012	2013	 2035
Mark	6	7	8	9	Α	В	С	D	 Z

Note (2) Production Month



Document Title	M101NWWB R3 Produc	Page No.	22/23		
Document No.		Issue date	2016/03/15	Revision	0 0

Month	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct	Nov.	Dec.
Mark	1	2	3	4	5	6	7	8	9	Α	В	С

Note (3) Production Day: 1~V. Code 20~23: Serial Number.

9.0 General Precaution

9.1 Use Restriction

This product is not authorized for use in life supporting systems, aircraft navigation control systems, military systems and any other application where performance failure could be life-threatening or otherwise catastrophic.

9.2 Handling Precaution

- (1) Please mount LCD module by using mounting holes arranged in four corners tightly.
- (2) Do not disassemble or modify the module. It may damage sensitive parts inside LCD module, and may cause scratches or dust on the display. IVO does not warrant the module, if customers disassemble or modify the module.
- (3) If LCD panel is broken and liquid crystal spills out, do not ingest or inhale liquid crystal, and do not contact liquid crystal with skin. If liquid crystal contacts mouth or eyes, rinse out with water immediately. If liquid crystal contacts skin or cloths, wash it off immediately with alcohol and rinse thoroughly with water.
- (4) Disconnect power supply before handling LCD module.
- (5) Refrain from strong mechanical shock and /or any force to the module.
- (6) Do not exceed the absolute maximum rating values, such as the supply voltage variation, input voltage variation, variation in parts parameters, environmental temperature; etc otherwise LCD module may be damaged. It's recommended employing protection circuit for power supply.
- (7) Do not touch, push or rub the polarizer with anything harder than HB pencil lead. Use fingerstalls of soft gloves in order to keep clean display quality, when persons handle the LCD module for incoming inspection or assembly.
- (8) When the surface is dusty, please wipe gently with absorbent cotton or other soft material. When cleaning the adhesives, please use absorbent cotton wetted with a little petroleum benzene or other adequate solvent.
- (9) Wipe off saliva or water drops as soon as possible. If saliva or water drops contact with polarizer for a long time, they may causes deformation or color fading.
- (10) Protection film must remove very slowly from the surface of LCD module to prevent from electrostatic occurrence.
- (11) Because LCD module uses CMOS-IC on circuit board and TFT-LCD panel, it is very weak to electrostatic discharge, please be careful with electrostatic discharge. Persons who handle the module should be grounded through adequate methods.
- (12) Do not adjust the variable resistor located on the module.

9.3 Storage Precaution

- (1) Please do not leave LCD module in the environment of high humidity and high temperature for a long time.
- (2) The module shall not be exposed under strong light such as direct sunlight. Otherwise, display characteristics may be changed.
- (3) The module should be stored in a dark place. It is prohibited to apply sunlight or fluorescent light in storage.

9.4 Operation Precaution



Document Title	M101NWWB R3 Produc	Page No.	23/23		
Document No.		Issue date	2016/03/15	Revision	0 0

- (1) Do not connect or disconnect the module in the "Power On" condition.
- (2) Power supply should always be turned on/off by "Power On/Off Sequence".
- (3) Module has high frequency circuits. Sufficient suppression to the electromagnetic interference should be done by system manufacturers. Grounding and shielding methods may be important to minimize the interference.
- (4) After installation of the TFT module into an enclosure, do not twist nor bend the TFT module even momentary. At designing the enclosure, it should be taken into consideration that no bending/twisting forces are applied to the TFT module from outside. Otherwise the TFT module may be damaged.

9.5 Others

- (1) Ultra-violet ray filter is necessary for outdoor operation.
- (2) Avoid condensation of water which may result in improper operation or disconnection of electrode.
- (3) If the module keeps displaying the same pattern for a long period of time, the image may be "sticked" to the screen.
- (4) This module has its circuitry PCB's on the rear side and should be handled carefully in order not to be stressed.

9.6 Disposal

When disposing LCD module, obey the local environmental regulations.