

# MCUXpresso SDK Release Notes Supporting FRDM-KL25Z

## Contents

## 1 Overview

The MCUXpresso Software Development Kit (SDK) is a collection of software enablement for Microcontrollers that includes peripheral drivers, high-level stacks including USB and lwIP, integration with WolfSSL and mbed TLS cryptography libraries, other middleware packages, such as multicore support and FatFs, and integrated RTOS support for FreeRTOS™ OS. In addition to the base enablement, the MCUXpresso SDK is augmented with demo applications and driver example projects, and API documentation to help the customers quickly leverage the support of the MCUXpresso SDK.

For the latest version of this and other MCUXpresso SDK documents, see the MCUXpresso SDK homepage [MCUXpresso-SDK: Software Development Kit](#).

1	Overview.....	1
2	MCUXpresso SDK.....	1
3	Development Tools.....	2
4	Supported Development Systems.....	2
5	Release Contents.....	2
6	MCUXpresso SDK Release Package.....	3
7	MISRA Compliance.....	6
8	Known Issues.....	6
9	Change Log - Peripheral drivers.....	7
10	Change Log - Middleware.....	13
11	Change Log - RTOS.....	16
12	Revision History.....	17

## 2 MCUXpresso SDK

As part of the MCUXpresso software and tools, MCUXpressoSDK is the evolution of Kinetis SDK v2.0.0 includes support for both LPC and i.MX System-on-Chips (SoC). The same drivers, APIs, and middleware are still available with support for Kinetis, LPC, and i.MX silicon. The MCUXpresso SDK adds support for the MCUXpresso IDE v10.0.0, a new Eclipse-based toolchain that works with all



## Development Tools

MCUXpresso SDKs. Easily import your SDK into the new toolchain to have access to all of the available components, examples, and demos for your target silicon. In addition to the MCUXpresso IDE v10.0.0, support for the MCUXpresso Project Generator allows for easy cloning of existing SDK examples and demos, allowing users to easily leverage the existing software examples provided by the SDK for their own projects.

### NOTE

In order to make the life of our customers a bit easier, the filenames and source code in MCUXpresso SDK containing the legacy Freescale prefix 'FSL' has been left as is. The 'FSL' prefix has been redefined as the NXP Foundation Software Library.

## 3 Development Tools

The MCUXpresso SDK was compiled and tested with these development tools:

- Kinetis Design Studio IDE v3.2
- IAR Embedded Workbench for ARM version 7.80.4
- MDK-ARM Microcontroller Development Kit (Keil)<sup>®</sup> 5.21a
- Makefiles support with GCC revision v5-2016-q3 from ARM Embedded
- MCUXpresso IDE v10.0.0

## 4 Supported Development Systems

This release supports boards and devices listed in this table. Boards and devices in boldface were tested in this release:

**Table 1. Supported MCU devices and development boards**

Development boards	MCU devices
<b>FRDM-KL25Z</b>	MKL25Z128VFM4, MKL25Z128VFT4, MKL25Z128VLH4, <b>MKL25Z128VLK4</b> , MKL25Z32VFM4, MKL25Z32VFT4, MKL25Z32VLH4, MKL25Z32VLK4, MKL25Z64VFM4, MKL25Z64VFT4, MKL25Z64VLH4, MKL25Z64VLK4, MKL15Z128CAD4, MKL15Z128VFM4, MKL15Z128VFT4, MKL15Z128VLH4, MKL15Z128VLK4, MKL15Z32VFM4, MKL15Z32VFT4, MKL15Z32VLH4, MKL15Z32VLK4, MKL15Z64VFM4, MKL15Z64VFT4, MKL15Z64VLH4, MKL15Z64VLK4, MKL14Z32VFM4, MKL14Z32VFT4, MKL14Z32VLH4, MKL14Z32VLK4, MKL14Z64VFM4, MKL14Z64VFT4, MKL14Z64VLH4, MKL14Z64VLK4, MKL24Z32VFM4, MKL24Z32VFT4, MKL24Z32VLH4, MKL24Z32VLK4, MKL24Z64VFM4, MKL24Z64VFT4, MKL24Z64VLH4, MKL24Z64VLK4

## 5 Release Contents

This table provides an overview of the MCUXpresso SDK release package contents and locations.

**Table 2. Release contents**

Deliverable	Location
Boards	<install_dir>/boards
Demo applications	<install_dir>/boards/<board_name>/demo_apps
USB demo applications	<install_dir>/boards/<board_name>/usb_examples
Driver examples	<install_dir>/boards/<board_name>/driver_examples
RTOS examples	<install_dir>/boards/<board_name>/rtos_examples
Multicore examples	<install_dir>/boards/<board_name>/multicore_examples
Documentation	<install_dir>/docs
USB Documentation	<install_dir>/docs/usb
lwIP Documentation	<install_dir>/docs/lwip
Middleware	<install_dir>/middleware
lwIP stack	<install_dir>/middleware/lwip_<version>
DMA manager	<install_dir>/middleware/dma_manager_<version>
FatFS stack	<install_dir>/middleware/fatfs_<version>
Multicore stack	<install_dir>/middleware/multicore_<version>
SDMMC card driver	<install_dir>/middleware/sdmmc_<version>
USB stack	<install_dir>/middleware/usb_<version>
Driver, SoC header files, extension header files and feature header files, utilities	<install_dir>/devices/<device_name>
Cortex Microcontroller Software Interface Standard (CMSIS) ARM Cortex <sup>®</sup> -M header files, DSP library source	<install_dir>/CMSIS
Peripheral Drivers	<install_dir>/devices/<device_name>/drivers
Utilities such as debug console	<install_dir>/devices/<device_name>/utilities
RTOS Kernel Code	<install_dir>/rtos
Tools	<install_dir>/tools

## 6 MCUXpresso SDK Release Package

The MCUXpresso SDK release package contents are aligned with the silicon subfamily it supports. This includes the boards, CMSIS, devices, documentation, middleware, and RTOS support.

### 6.1 Device support

The device folder contains all available software enablement for the specific System-on-Chip (SoC) subfamily. This folder includes clock-specific implementation, device register header file, device register feature header file, CMSIS derived device SVD, and the system configuration source files. Included with the standard SoC support are folders containing peripheral drivers, toolchain support, and a simple debug console.

The device-specific header files provide a direct access to the MCU peripheral registers. The device header file provides an overall SoC memory mapped register definition. In addition to the overall device memory mapped header file, the MCUXpresso SDK also includes the feature header file for each peripheral instantiated on the SoC.

The toolchain folder contains the startup code and linker files for each supported toolchain. The startup code is a CMSIS-compliant startup that efficiently transfers the code execution to the main() function.

### 6.1.1 Board support

The boards folder provides the board-specific demo applications, driver examples, RTOS, and middleware examples.

### 6.1.2 Demo applications and other examples

The demo applications demonstrate the usage of the peripheral drivers to achieve a system level solution. Each demo application contains a readme file that describes the operation of the demo and required setup steps.

The driver examples demonstrate the capabilities of the peripheral drivers. Each example implements a common use case to help demonstrate the driver functionality.

The RTOS and middleware folders each contain examples demonstrating the use of the included source.

## 6.2 Middleware

### 6.2.1 USB stack

See the *MCUXpresso SDK USB Stack User's Guide* (document USBSUG) for more information.

#### 6.2.1.1 Peripheral devices tested with the USB Host stack

This table provides a list of USB devices tested with the USB Host stack.

**Table 3. Peripheral devices**

Device type	Device
USB HUB	BELKIN F5U233
	BELKIN F5U304
	BELKIN F5U307
	BELKIN F4U040
	UNITEK Y-2151
	Z-TEK ZK032A
USB flash drive	HYUNDAI HY-HB608
	ADATA C008 32 GB
	ADATA S102 8 G
	ADATA S102 16 G
	Verbatim STORE N GO USB Device 8 G

*Table continues on the next page...*

**Table 3. Peripheral devices (continued)**

	Kingston DataTraveler DT101 G2 SanDisk Cruzer Blade 8 GB Unisplendour 1 G Imation 2 GB V-mux 2 GB Sanmina-SCI 128 M Corporate Express 1 G TOSHIBA THUHYBS-008G 8 G Transcend JF700 8 G Netac U903 16 G SSK SFD205 8 GB Rex 4 GB SAMSUNG USB3.0 16GB
USB card reader/adaptor	SSK TF adapter Kawau Multi Card Reader Kawau TF adapter Kawau SDHC card
USB Mouse	DELL MS111-P DELL M066U0A DELL MUAVDEL8 TARGUS AMU76AP DELL MD56U0 DELL MS111-T RAPOO M110
USB Keyboard	DELL SK8135 DELL SK8115

## 6.2.2 TCP/IP stack

The lwIP TCP/IP stack is pre-integrated with MCUXpresso SDK and runs on top of the MCUXpresso SDK Ethernet driver with Ethernet-capable devices/boards. For details, see the *lwIP TCP/IP Stack and MCUXpresso SDK Integration User's Guide* (document MCUXSDKLWIPUG).

## 6.2.3 File System

The FatFs file system is integrated with MCUXpresso SDK and can be used to access either the SD card or the USB memory stick when the SD card driver or the USB Mass Storage Device class implementation is used.

For details, see the FatFs documentation installed at <install\_dir>/middleware/fatfs\_<version>/doc.

## 6.2.4 RTOS

The MCUXpresso SDK is integrated with FreeRTOS OS.

## 6.2.5 CMSIS

The MCUXpresso SDK is shipped with the standard CMSIS development pack, including the prebuilt libraries.

# 7 MISRA Compliance

All MCUXpresso SDK drivers and USB stack comply to MISRA 2004 rules with the following exceptions.

Exception Rules	Description
1.1	All code shall conform to ISO 9899:1990 Programming languages - C, amended and corrected by ISO/IEC 9899/COR1:1995, ISO/IEC 9899/AMD1:1995, and ISO/IEC
2.4	Sections of code should not be commented out.
5.1	Identifiers (internal and external) shall not rely on the significance of more than 31 characters.
6.3	typedefs that indicate size and signedness should be used in place of the basic types.
6.4	Bitfields shall only be defined to be of type unsigned int or signed int.
8.1	Functions shall have prototype declarations and the prototype shall be visible at both the function definition and call.
8.5	There shall be no definitions of objects or functions in a header file.
8.1	All declarations and definitions of objects or functions at file scope shall have internal linkage unless external linkage is required.
8.12	When an array is declared with external linkage, its size shall be stated explicitly or defined implicitly by initialization.
	The value of an expression of integer type shall not be implicitly converted to a different underlying type if:
	a. it is not a conversion to a wider integer type of the same signedness, or
	b. the expression is complex, or
	c. the expression is not constant and is a function argument, or
10.1	d. the expression is not constant and is a return expression.
10.3	The value of a complex expression of integer type shall only be cast to a type that is not wider and of the same signedness as the underlying type of the expression.
11.3	A cast should not be performed between a pointer type and an integral type.
11.4	A cast should not be performed between a pointer to object type and a different pointer to object type.
11.5	A cast shall not be performed that removes any const or volatile qualification from the type addressed by a pointer.
12.2	The value of an expression shall be the same under any order of evaluation that the standard permits.
12.4	The right-hand operand of a logical && or    operator shall not contain side effects.
12.6	The operands of logical operators (&&,   , and !) should be effectively boolean. Expressions that are effectively boolean should not be used as operands to operators other than (&&,   , !, =, ==, !=, and ?.).
12.13	The increment (++) and decrement (--) operators should not be mixed with other operators in an expression.
14.3	Before preprocessing, a null statement shall only occur on a line by itself; it may be followed by a comment, provided that the first character following the null statement is a whitespace character.
14.5	The continue statement shall not be used.
14.7	A function shall have a single point of exit at the end of the function.
16.1	Functions shall not be defined with a variable number of arguments.
17.4	Array indexing shall be the only allowed form of pointer arithmetic.
18.4	Unions shall not be used.
19.1	#include statements in a file should only be preceded by other preprocessor directives or comments.
19.1	In the definition of a function-like macro, each instance of a parameter shall be enclosed in parentheses unless it is used as the operand of # or ##.
20.4	Dynamic heap memory allocation shall not be used.
20.9	The input/output library <stdio.h> shall not be used in production code.

Figure 1. MISRA exceptions

## 8 Known Issues

## 8.1 Maximum file path length in Windows® 7 Operating System

Windows 7 operating system imposes a 260 character maximum length for file paths. When installing the MCUXpresso SDK, place it in a directory close to the root to prevent file paths from exceeding the maximum character length specified by the Windows operating system. The recommended location is the C:\nxp folder.

## 8.2 USB HUB Power supply

The external power supply of the USB HUB must be provided before it can be used. The development board power is not enough to supply multi-level USB HUBs and connected devices. Therefore, the external USB HUB that is connected to the development board should have its own power supply.

## 8.3 USBFS controller issue

Because of the USBFS controller design issues, the USB host suspend/resume demos (usb\_suspend\_resume\_host\_hid\_mouse) of the full speed controller do not support the low speed device directly.

## 8.4 USB PID issue

Because the PID of all USB device examples is updated, uninstall the device drivers and then reinstall when the device (with new PID) is plugged in the first time.

## 8.5 Some ISSDK 1.0 projects do not work with ARMGCC Toolchain

Some of ISSDK 1.0 projects have a problem with inclusion of files with the wrong case alignment. This causes the builds to fail for the ARMGCC toolchain under the Linux OS

## 8.6 FreeRTOS issue

When generating a new FreeRTOS project with New Project Wizard tool, the user should deassert the micro option "configUSE\_PORT\_OPTIMISED\_TASK\_SELECTION" in the "FreeRTOSConfig.h" file while it is not used in the template project for some Cortex-M0+ devices, or it might not pass the compiling.

# 9 Change Log - Peripheral drivers

### ADC16

The current ADC16 driver version is 2.0.0

- 2.0.0
  - Initial version

## Change Log - Peripheral drivers

### CMP

The current CMP driver version is 2.0.0

- 2.0.0
  - Initial version

### COP

The current COP driver version is 2.0.0

- 2.0.0
  - Initial version

### DAC

The current DAC driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - Bug fix:
    - Moved the default DAC\_Enable(..., true) from the DAC\_Init() to the application code to enable the DAC output

### DMA

The current DMA driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - Bug fix:
    - Fixed the DMA driver build fail by adding parenthesis. The issue occurs because of the MISRA C 2004 rule 12.5

### DMAMUX

The current DMAMUX driver version is 2.0.2

- 2.0.0
  - Initial version
- 2.0.1
  - Bug fix:
    - Fixed build warning while setting the DMA request source in the DMAMUX\_SetSourceChange issue by changing the type of the parameter source from uint8\_t to uint32\_t
- 2.0.2
  - New feature:
    - Added the *always on enable* feature of a DMA channel for the ULP1 DMAMUX support

### Flash

The current Flash driver version is 2.3.1

- 2.0.0
  - Initial version
- 2.1.0
  - New features:
    - Support for the FTFLL device in FLASH\_Swap API
    - Support for various pflash start addresses
    - Added support for KV58 in the cache clear function
  - Bug fix



- Compiled execute-in-RAM functions as a PIC binary code for driver use
- Added missed FlexRAM properties
- Fixed an unaligned variable issue for the execute-in-RAM function code array
- 2.2.0
  - New features:
    - Support FTL device in FLASH\_Swap API
    - Support various pflash start addresses
    - Add support for KV58 in cache clear function
    - Add support for device with secondary flash (KW40)
  - Bug fix
    - Compiled execute-in-ram functions as PIC binary code for driver use
    - Added missed flexram properties
    - Fixed unaligned variable issue for execute-in-ram function code array
- 2.3.0
  - New features:
    - Add support for device with LP flash (K3S/G)
    - Add flash prefetch speculation APIs
  - Improvement
    - Refine flash\_cache\_clear function
    - Reorganize the member of flash\_config\_t struct
- 2.3.1
  - Bug fix
    - Unified Flash IFR design from K3
    - New encoding rule for K3 flash size

## GPIO

The current GPIO driver version is 2.1.1

- 2.1.0
  - API Interface Change:
    - Added "pins" or "pin" to some API names
    - Renamed the "GPIO\_PinConfigure" to "GPIO\_PinInit"
- 2.1.1
  - API Interface Change
    - Added API for the check attribute bytes

## I2C

The current I2C driver version is 2.0.3

- 2.0.1
  - New features
    - Added a double buffer enable configuration for SoCs which have the DFEN bit in S2 register
    - Added the flexible transmit/receive buffer size support in I2C\_SlaveHandleIRQ
    - Added the start flag clear address match and release bus operation in I2C\_SlaveWrite/ReadBlocking API
  - Bug fix:
    - Updated the kI2C\_SlaveRepeatedStartEvent to kI2C\_SlaveStartEvent
- 2.0.2
  - Bug Fix:
    - Fixed the issue that occurs in master receive and slave transmit mode with no stop flag and master can't start a next transfer because it can't send out restart signal
    - Fixed a data transfer out of order issue which occurs because of a memory barrier
  - New Features:

## Change Log - Peripheral drivers

- Added an address nak event for the master.
- Added a general call event for the slave.
- 2.0.3
  - Bug fix
    - Remove enableHighDrive member in the master/slave configuration structure because the operation to HDRS bit is useless. The user needs to use DSE bit in port register to configure the high drive capability.
    - Add reset registers operation in I2C\_MasterInit and I2C\_SlaveInit APIs, and fix the issue that I2C could not switch between master and slave mode.
    - Improve slave IRQ handler to handle the corner case that stop flag and address match flag come synchronously.

## LLWU

The current LLWU driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - Changes:
    - Updated for KL8x
- 2.1.1
  - Bug fix:
    - Disable the auto stop feature in the EDMA driver. Previously the autostop feature is enabled at transfer when transfer with stop flag. If the previous transfer is without stop flag, then when starting a new transfer with stop flag, because the auto stop feature is enabled, the stop flag sends before starting the new transfer and the start flag can not successfully sent, so the transfer cannot start.
    - Change default slave configuration with address stall false

## LPSCI

The current LPSCI driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - Updated the baudrate code. Before setting a baudrate, check whether the value is valid or not. If the value is not valid, don't change the baudrate and return
  - Removed needless check of event flags and assert in LPSCI\_RTOS\_Receive
  - Wait always for RX event flag in LPSCI\_RTOS\_Receive

## LPTMR

The current LPTMR driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - Driver update
    - Update the LPTMR driver due to the register LPTMRx\_CMRCNR in some devices that have become 32-bit, so that the updated LPTMR driver supports the 32 bit CNR and CMR register.

## PIT

The current PIT driver version is 2.0.0

- 2.0.0

- Initial version

## PMC

The current PMC driver version is 2.0.0

- 2.0.0
  - Initial version

## PORT

The current PORT driver version is 2.0.2

- 2.0.1
  - Changes:
    - Added "const" in function parameters
    - Updated enumeration variable names
- 2.0.2
  - Changes:
    - Added feature guard macros in the driver

## RCM

The current RCM driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - [KPSDK-10249] Fixed the kRCM\_SourceSw bit shift issue.

## RTC

The current RTC driver version is 2.0.0

- 2.0.0
  - Initial version

## SIM

The current SIM driver version is 2.0.0

- 2.0.0
  - Initial version

## SMC

The current SMC driver version is 2.0.3

- 2.0.0
  - Initial version
- 2.0.1
  - Changes:
    - Updated for KL8x
- 2.0.2
  - Bug fix:
    - Added DSB before WFI and ISB after WFI
  - Changes:
    - Updated the SMC\_SetPowerModeVlpw implementation
- 2.0.3
  - Add APIs SMC\_PreEnterStopModes, SMC\_PreEnterWaitModes, SMC\_PostExitWaitModes, and SMC\_PostExitStopModes

### SPI

The current SPI driver version is 2.0.1

- 2.0.0
  - Initial version
- 2.0.1
  - Bug fix
    - Fixed the SPI\_Enable function parameter error
    - Set the s\_dummy variable as a static variable in fsl\_spi\_dma.c
  - Optimization
    - Optimizes the code size when not using the transactional API
    - Improved performance in a polling method

### TPM

The current TPM driver version is 2.0.2

- 2.0.0
  - Initial version
- 2.0.1
  - Bug fix:
    - Fixed the TPM\_UpdateChnEdgeLevelSelect ACK wait issue.
    - Fixed the TPM\_SetupDualEdgeCapture failure to set the FILTER register.
    - Fixed the TPM\_UpdateChnEdgeLevelSelect ACK wait issue.
- 2.0.2
  - Bug fix:
    - Fixed issues in TPM\_SetupPwm/TPM\_UpdateChnEdgeLevelSelect /TPM\_SetupInputCapture/TPM\_SetupOutputCompare/TPM\_SetupDualEdgeCapture functions wait acknowledgement when the channel is disabled.

### UART

The current UART driver version is 2.1.4

- 2.0.0
  - Initial version
- 2.1.0
  - Add transactional APIs
- 2.1.1
  - Removed needless check of event flags and assert in UART\_RTOS\_Receive
  - Wait always for RX event flag in UART\_RTOS\_Receive
- 2.1.2
  - Fix baud rate fine adjust bug to make the computed baud rate more accurate
- 2.1.3
  - Add rx framing error and parity error status check when use interrupt transfer
- 2.1.4
  - Change parameter type in UART\_RTOS\_Init() struct rtos\_uart\_config -> uart\_rtos\_config\_t
  - Bug fixed:
    - Disable UART receives interrupts instead of disabling all NVIC when reading data from a ring buffer. When a ring buffer is used, receive non-blocking disables all NVIC interrupts to protect the ring buffer, which will have a negative effect on other IPS using the interrupts.

### CLOCK

The current CLOCK driver version is 2.2.1

- 2.0.0
  - Initial version
- 2.1.0
  - Changes:
    - Merged the fsl\_mcg and fsl\_osc into fsl\_clock
- 2.2.0
  - New features:
    - [KPSDK-9157] Updated the CLOCK\_SetFeiMode/CLOCK\_SetFbiMode/CLOCK\_BootToFeiMode() to support set MCG\_C4[DMX32]=1 in FEI/FBI modes
  - Bug fix:
    - Updated the IP\_CLOCKS array, removed unused gates, and added missing gates
- 2.2.1
  - Bug fix:
    - Fix the issue that MCG could not switch to FEE/FBE/PBE modes when the OSCERCLK clock is not enabled

## 10 Change Log - Middleware

### DMA Manager

The current DMA Manager driver version is 2.1.0

- 2.0.0
  - Initial version
- 2.1.0
  - Update DMA manager interface to support dynamic configure the manage area. This is used for platform with multiple cores

### FatFs

The current FatFs driver version is R0.12b

- R0.12b\_rev0
- R0.11a
  - Added glue functions for low level drivers (SDHC, SDSPI, RAM, and MMC) and modified the diskio.c file
  - Added RTOS wrappers to make FatFs thread-safe. Modified the syscall.c file
  - Renamed ffconf.h file to ffconf\_template.h file. Each application should contain its own ffconf.h file
  - Conditional compilation of physical disk interfaces in diskio.c

### SDMMC

The current SDMMC driver version is 2.1.2

- 2.1.0
  - Bug fix:
    - Changed the callback mechanism when sending a command
    - Fixed the performance low issue when transferring data
  - Changes:
    - Changed the name of error codes returned by an internal function
    - Merged all host-related attributes into one structure
    - Optimized the function to set a maximum data bus width for the MMC card
- 2.1.1

## Change Log - Middleware

- Bug fix:
  - Fixed the block range boundary error when transferring data to the MMC card
  - Fixed the bit mask error in the SD card when switching to a high-speed function
- Changes:
  - Added an error code to indicate that SDHC ADMA1 transfer type is not supported
  - Optimized the SD card initialization function
- 2.1.2
  - New feature
    - Add fsl\_host.h to provide prototype to adapt different controller IPs(SDHC/SDIF)
    - Add adaptor code in sdmmc/port folder to adapt different host controller IPs with different transfer modes(int/polling/freertos). Application include different adaptor code to make application simpler
    - Adaptor code provides HOST\_Init/HOST\_Deinit/CardInsertDetect APIs to do host controller initialize and transfer function configuration. SDMMC card stack uses adaptor code inside stack to wait card insert and configure host when calling card init APIs (SD\_Init/MMC\_Init/SDIO\_Init)
    - So this change requires user to include host adaptor code into application. If not, link errors for cannot find the definition of HOST\_Init/HOST\_Deinit/CardInsertDetect will appear
  - New feature
    - Improve SDMMC to support SD v3.0 and EMMC v5.0
  - Bug fix:
    - Fix wrong comparison between count and length in MMC\_ReadBlocks/MMC\_WriteBlocks

## USB stack

The current USB stack version is 1.6.3

- 1.0.0
  - New features:
    - Supported roles
      - Device
      - Host
    - Supported controllers
      - KHCI (full-speed)
      - EHCI (high-speed)
    - Supported classes
      - AUDIO
      - CCID
      - CDC
      - HID
      - MSC
      - PHDC
      - VIDEO
    - Examples
      - usb\_device\_audio\_generator
      - usb\_device\_audio\_speaker
      - usb\_device\_ccid\_smart\_card
      - usb\_device\_cdc\_vcom
      - usb\_device\_cdc\_vnic
      - usb\_device\_composite\_cdc\_msc
      - usb\_device\_composite\_hid\_audio
      - usb\_device\_composite\_hid\_mouse\_hid\_keyboard
      - vusb\_device\_hid\_generic
      - usb\_device\_hid\_mouse
      - usb\_device\_msc\_ramdisk
      - usb\_device\_msc\_sdcard
      - usb\_device\_phdc\_weighscale

- usb\_device\_video\_flexio\_ov7670
- usb\_device\_video\_virtual\_camera
- usb\_host\_audio\_speaker
- usb\_host\_cdc
- usb\_host\_hid\_generic
- usb\_host\_hid\_mouse
- usb\_host\_hid\_mouse\_keyboard
- usb\_host\_msdc\_command
- usb\_host\_msdc\_fatfs
- usb\_host\_phdc\_manager
- usb\_keyboard2mouse
- usb\_pin\_detect\_hid\_mouse
- 1.0.1
  - Bug fix
    - Improved the device audio speaker efficiency by changing the transfer mode from interrupt to DMA to eliminate the periodic noise
- 1.1.0
  - Bug fix:
    - Fixed issues in the USB certification
    - Updated the VID and Manufacturer string to NXP Semiconductors
  - New features:
    - Supported classes
      - Printer
    - Examples
      - usb\_device\_composite\_cdc\_msc\_sdcard
      - usb\_device\_printer\_virtual\_plain\_text
      - usb\_host\_printer\_plain\_text
  - Changes:
    - Renamed example usb\_device\_composite\_cdc\_msc to usb\_device\_composite\_cdc\_msc\_ramdisk
- 1.2.0
  - New features:
    - Supported controllers
      - LPC IP3511 (Full speed, device mode)
- 1.3.0
  - New features:
    - Supported roles
      - OTG
    - Supported classes
      - CDC RNDIS
    - Examples
      - usb\_otg\_hid\_mouse
      - usb\_device\_cdc\_vnic
      - usb\_suspend\_resume\_device\_hid\_mouse
      - usb\_suspend\_resume\_host\_hid\_mouse
- 1.4.0
  - New features:
    - Examples
      - usb\_device\_hid\_mouse/freertos\_static
      - usb\_suspend\_resume\_device\_hid\_mouse\_lite
- 1.5.0
  - New features:
    - Supported controllers
      - OHCI (Full Speed, Host mode)
      - IP3516 (High Speed, Host mode)
      - IP3511 (High Speed, Device mode)

## Change Log - RTOS

- 1.6.0
  - New features:
    - Supported Device Charger Detect feature on usb\_device\_hid\_mouse
- 1.6.1
  - New features:
    - Change the struct variable address method for device\_video\_virtual\_camera and host\_phdc\_manager
- 1.6.2
  - New features:
    - Multi instance support
- 1.6.3
  - Bug fix:
    - -IP3511\_HS driver control transfer sequence issue, enable 3511 ip cv test

# 11 Change Log - RTOS

## FreeRTOS OS

The current version is FreeRTOS OS 9.0.0. The original package is available at [freertos.org](http://freertos.org).

- 9.0.0\_rev2
  - New features:
    - Enabled MCUXpresso thread aware debugging. Added freertos\_tasks\_c\_additions.h and configINCLUDE\_FREERTOS\_TASK\_C\_ADDITIONS\_H and configFRTOS\_MEMORY\_SCHEME macros
- 9.0.0\_rev1
  - New features:
    - Enable -flto optimization in GCC by adding **attribute((used))** for vTaskSwitchContext
    - Enable KDS Task Aware Debugger. Apply FreeRTOS patch to enable configRECORD\_STACK\_HIGH\_ADDRESS macro. Modified files are task.c and FreeRTOS.h
- 9.0.0\_rev0
  - New features:
    - Example freertos\_sem\_static
    - Static allocation support RTOS driver wrappers
  - Other changes:
    - Tickless idle rework. Support for different timers is in separated files (fsl\_tickless\_systick.c, fsl\_tickless\_lptmr.c)
    - Remove configuration option configSYSTICK\_USE\_LOW\_POWER\_TIMER. Low power timer is now selected by linking of appropriate file fsl\_tickless\_lptmr.c
    - Remove configOVERRIDE\_DEFAULT\_TICK\_CONFIGURATION in RVDS port. Use of **attribute((weak))** is preferred solution. Not same as `_weak`
- 8.2.3
  - New features:
    - Added tickless idle mode support
    - Added a template application for Kinetis Expert (KEx) tool (template\_application)
  - Changes:
    - Reduced the folder structure to keep only Kinetis-related information



## 12 Revision History

This table summarizes revisions to this document.

**Table 4. Revision history**

<b>Revision number</b>	<b>Date</b>	<b>Substantive changes</b>
0	03/2017	Initial release

**How to Reach Us:****Home Page:**[nxp.com](http://nxp.com)**Web Support:**[nxp.com/support](http://nxp.com/support)

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: [nxp.com/SalesTermsandConditions](http://nxp.com/SalesTermsandConditions).

NXP, the NXP logo, Freescale, the Freescale logo, and Kinetis are trademarks of NXP B.V. All other product or service names are the property of their respective owners. ARM, ARM Powered, and Cortex are registered trademarks of ARM Limited (or its subsidiaries) in the EU and/or elsewhere. All rights reserved.

© 2017 NXP B.V.

Document Number MCUXSDKKL25ZRN  
Revision 0, 03/2017

