Accelerate Development of
Robust Network Communications
with CANopen and CANopen FD

Olaf Pfeiffer, Shelby Unger APRIL 21, 2020



SECURE CONNECTIONS FOR A SMARTER WORLD







#### THE MCUXPRESSO ECOSYSTEM



### Core Technologies from NXP

- MCUXpresso IDE
- MCUXpresso SDK
- MCUXpresso Config Tools
- MCUXpresso Secure Provisioning Tool

# > Enabling Software Technologies

- Run time software libraries and middleware
- Enable customers to focus on differentiation
- From NXP and partners

### > Enabling Tools Technologies

- Partner IDEs
- Debug Probes
- Development Boards
- From NXP and partners



#### MCUXPRESSO SDK

#### SOFTWARE FRAMEWORK AND DRIVERS



#### Architecture:

- CMSIS-CORE compatible
- Single driver for each peripheral
- Transactional APIs w/ optional DMA support for communication peripherals

#### **Integrated RTOS:**

- Amazon FreeRTOS
- RTOS-native driver wrappers

#### **Enabling Technologies:**

- Wired and wireless connectivity
- Graphics/HMI
- Motor Control
- ML/Al
- Cloud connectivity
- Storage
- · ...and more

#### Reference Software:

- Peripheral driver usage examples
- Application demos
- FreeRTOS usage demos
- IoT connectivity examples

#### License:


- BSD 3-clause for startup, drivers, USB stack
- · All code Black Duck scanned

#### **Toolchains:**

- MCUXpresso IDE
- IAR®, ARM® Keil®, GCC w/ Cmake

#### Quality:

- · Production-grade software
- MISRA 2004 compliance
- Checked with Coverity® static analysis tools













#### NOW AVAILABLE IN THE MCUXPRESSO SDK





NXP has partnered with EmSA to offer CANopen as an Enabling Software Technology. **Fully integrated** CANopen Libraries based on MicroCANopen Plus v7.0 are available in MCUXpresso SDK v2.7.



#### Libraries

A limited version of MicroCANopen Plus is included in MCUXpresso SDK for select devices in library form:

- i.MX RT1050
   LPC54628
- i.MX RT1060 LPC54618
- i.MX RT1064
   LPC54608
- i.MX RT1020
   LPC54S018
  - LPC551x/S1x (coming soon)



#### Examples

Examples are available to help you get started with your CAN application.

- 1. CANopen Generic I/O example (CiA 401)
- 2. CANopen Manager example




Go beyond the examples and seamlessly transition from evaluation to full production software development.

CANopen Architecture software is available as a free download to help you easily generate custom configurations.



#### LPC551X/S1X MCU FAMILY BLOCK DIAGRAM



#### **Core Platform**

- Up to 150MHz Cortex-M33
- Multilayer Bus Matrix

#### **Memory**

- Up to 256KB FLASH
- Up to 96KB RAM
- 128KB ROM

#### **Timers**

- 5 x 32b Timers
- SCTimer/PWM
- · Muiti-Rate Timer
- Windowed Watchdog Timer
- RTC
- Micro Timer

#### Interfaces

- USB High-speed (H/D) w/ on-chip HS PHY USB Full-speed (H/D), Crystal-less
- 1 x High-Speed SPI up to 50MHz
- 8 x Flexcomms support up to 8x SPI, 8x I2C, 8x UART, 4x I<sup>2</sup>S channels (total 8 instances)
- CAN-FD (CAN 2.0 on LPC5512)

- High Efficiency Cortex-M33
- Advanced Security
- CAN-FD and USB HS
- 10K RSL \$0.97-\$1.80

#### **Advanced Security**

- TrustZone-M
- Protected Flash Region (PFR)
- AES-256 HW Encryption/Decryption Engine
- SHA-2
- CASPER Co-Processor for Assymetric cryptography
- SRAM PUF for Key Generation support
- PRINCE Real-time Encrypt/Decrypt for flash data
- Secure debug authentication
- RNG

#### **Analog**

- 1 16b ADC, up to 10 ch, 2MSPS
- Analog Comparator
- Temperature Sensor

#### **Packages**

- HLQFP100
- VFBGA98
- HTQFP64

#### Other

- Buck DC-DC
- Operating voltage: 1.8 to 3.6V
- Temperature range: -40 to 105 °C



#### LPC551X/S1X TARGET APPLICATIONS

#### **Target Applications**



#### **Industrial & Building Automation**

- Remote IO and Sensor Nodes
- Elevators and Lifts
- Smart Lighting and Utilities



#### **Consumer Products**

- Gaming and PC Peripherals
- Vehicle/Asset Tracking Systems
- Cordless Power Tools and Appliances



#### **Smart Home**

- Secure/Biometric Access Control
- Security Systems
- Sensor Nodes

#### **Benefits**

#### **Industrial & Building Automation**

- 150Mhz Cortex-M33 & package flexibility for compact design
- High precision & High Speed ADC
- CAN-FD for an upgrade from CAN2.0

#### Consumer

- HS/FS USB with PHY built-in for BOM cost saving
- High-Speed SPI for efficient module interface
- Secure boot supports FW update
- Large SRAM for easy FW development
- Low power consumption

#### **Smart Home & Sensor Node**

- Trust Zone for memory protection
- PRINCE for real-time de-/encryption for embedded flash
- Built-in SRAM PUF for key storage



# **MCU**Xpresso Software and Tools UNIFIED SUITE OF TOOLS FOR EASY DEVELOPMENT WITH NXP MCUs Secure Prov

# MCUXPRESSO SOFTWARE AND TOOLS ADDITIONAL WEB RESOURCES



MCUXpresso Software and Tools Overview Page:

https://www.nxp.com/mcuxpresso

MCUXpresso Software and Tools Community Site:

https://community.nxp.com/community/mcuxpresso







Community



Support devices

Supported Devices Table (Community Doc)

CAN (FD) overview

Wired Communications on NXP MCUs







# CANopen (FD) hands-on with NXP's MCUXpresso SDK www.em-sa.com/nxp



SECURE CONNECTIONS FOR A SMARTER WORLD

Olaf Pfeiffer Embedded Systems Academy





#### PREREQUISITES: SOFTWARE & "HOW TO"

# NXP's MCUXpresso SDK

- Check introductory videos and webinars www.em-sa.com/video
- SDK Builder at mcuxpresso.nxp.com
- EmSA CANopen Libraries included for selected NXP MCUs

# EmSA's CANopen (FD)

- Check introductory videos and webinars www.em-sa.com/video
- CANopen Configuration: CANopen Architect Mini www.em-sa.com/nxp
- CANopen Monitor: for example CANopen Magic Lite




#### PREREQUISITES: HARDWARE

# NXP LPC55S16-EVK

 Runs the CANopen FD example which we will modify/enhance during this session

CAN FD interface

For example PCAN-USB FD




#### **GET SW FROM SDK BUILDER**


**Embedded Wizard** 

Middlewore









Embedded Wizard CIII



#### **Hardware Details**

LPCXpresso54608 Board

LPC54608 Device

Core Type / Cortex-M4F / 180MHz

Max Freq

Device 512 KB Flash 192 KB RAM Memory Size

#### SDK Details

2.7.0 (released 2019-12-19) SDK Version:

Host OS: Windows

Toolchain: All Toolchains

Middleware: CMSIS DSP Library, canopen,

mbedtls, sdmmc stack

### **CANOPEN (FD) BASICS: OBJECT DICTIONARY**

- Object Dictionary
  - -Each CANopen (FD)node has one
  - -Contains all parameters (config & data) that can be communicated



Node ID 5				
Name	Index	Sub	Тур	Data
Device Type	1000h	0	U32	00000191h
Heartbeat	1017h	0	U16	500
Serial Nr	1018h	4	U32	010E4FF1h
Digital In 1	6000h	1	U8	5Ah

# CANOPEN (FD) BASICS: (U)SDO & PDO



# (U)SDO Communication

- (Universal) Service Data Object
- Access to one OD entry in one node (request/response)



# **PDO Communication**

- Process Data Object
- Group multiple OD entries into one message (multicast/broadcast)



#### HANDS-ON SESSION LPC55S16-EVK

# CANopen Device Demo

- -Replace process data
  - Receive PDO 1: single command byte for switching operating mode
  - Transmit PDO 1: three analog 16bit values from accelerometer
  - Transmit PDO 2:
     32bit loop counter for diagnostics

- -String manipulation
  - Uses 128char string buffer
  - Show use of data sizes bigger than 32bit
  - Changes with operating mode switch



# Hands-on using: MCUXpresso SDK **CANopen Architect Mini CANopen Magic Lite**





www.em-sa.com/nxp www.em-sa.com/video

# SECURE CONNECTIONS FOR A SMARTER WORLD